



**NOTES:**

1. MATERIALS:  
BODY - BRASS, NICKEL PLATED  
CONTACTS - BRASS, NICKEL PLATED  
INSULATOR - ABS  
HEX NUT - DIE CAST, NICKEL PLATED
2. HEX NUT TO BE SHIPPED ASSEMBLED TO THE BODY OF JACK.
3. THIS PART IS RoHS COMPLIANT.

PART NUMBER	CENTER PIN DIAMETER
721AFMS	0.083 [2.1mm]
712AFMS	0.098 [2.5mm]

**CUSTOMER DRAWING**

						THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.
					UNLESS OTHERWISE SPECIFIED	SIZE
					1. ALL DIMENSIONS IN INCHES [mm]	WIDTH
					- TWO PLACE DECIMALS ±0.02 [0.5]	MULT
					- THREE PLACE DECIMALS ±0.005 [0.13]	LBS/M
						TEMPER
					FINISH	
					SPEC No.	MATERIAL
					FIRST USED ON	SPEC No.
					SCALE	
					3:1	
					DATE DRAWN	BY
					8/28/17	CHKD
					TJK	TJK
					8/28/17	APVD
					8/28/17	TJK
A	27939	9/6/17	TJK	TJK		
REV	ECO NUMBER	DATE	BY	APVD	NAME	FRONT MOUNT SHIELDED POWER JACK, RoHS
						PART No.
						712AFMS_721AFMS
						REV
						A
REVISIONS					DO NOT SCALE DRAWING	