






COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,
IT MAY NEITHER BE DUPLICATED NOR MADE AVAILABLE TO A THIRD PARTY.
AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.



PCB 09-15



PCB 15-26, 26-44 or 37-62



CTxx*1)S1-5000

e.g. CT15-26S1-5000

*1) xx No. of contacts 09-15, 15-26, 25-44 or 37-62

xx *1)	A [mm]	B [mm]	C [mm]	H [mm]	J [mm]	No. of Contacts 1./2./3. row
09-15	30.8	16.4	25	7.1	2.29	5/5/5
15-26	39.1	24.7	33.3	6.8	2.29	9/9/8
25-44	53	38.5	47.04	7	2.29	15/15/14
37-62	69.3	54.9	63.5	7	2.42	21/21/20

4	2	Snap-in bolt	PCB 1.6mm / Brass	tin plated
3	xx	Signal contact	HS1 / Brass	0.3µm Au
2	1	Shell	Steel	tin plated
1	1	Insulator	Thermoplastic, GF UL 94V-0	
No.	St.	Part	Type Description/Material	Surface plating/Colour/Class

Measurement without tolerance occ. to ISO 2768-m	SCALE 2:1	TITLE	High Density D-Sub Connector	
NAME / DATE Markus.Jobst 22-02-2012				
DRAWN sschref 22-02-2012				
CHECKED				
FCT a molex company		DWG.NO.	CTxxS1-5000	REV. 1
REV.	DATE	CH.-NO.	ORIGINAL: DIN A3-DRAWING AS A FILE	REPLACEMENT FOR: CT09-15S1-5000
				PAGES 1