

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20




COPYRIGHT 20


BY -

ALL RIGHTS RESERVED.


SUGGESTED MATING TAB





TOP VIEW

FOR 1 CIRCUIT
SIDE VIEWFOR 2 CIRCUIT
SIDE VIEW
(6MM PITCH)

TYPE A (When using tab shoulder for butting)



TOP VIEW

FOR 2 CIRCUIT
SIDE VIEW
(6MM PITCH)


TYPE B (When using resin, etc. for butting)

Shapping of the
tab's hole must
not exceed 0.08mm

NOTE:

1. HOUSING MATERIAL, NYLON 6/66, GLASS-FIBRE. UL94V-0.
2. GWT 750°C VERSION ACCORDING TO ICE 60335-1.
3. CONTACT MATERIAL, TIN PLATED BRASS.

4 NEW PART NUMBER WITH DIFFERENT PACKAGING QTY.
AND SMALLER REELING SIZE (24in).



SECTION B-B

SECTION A-A



4.5 REF.	4.6	3.2 REF.	3.0	2.29-3.30	20-16	3-2299286-2
3.4 REF.	4.1	2.1 REF.	2.3	1.52-2.79	24-20	3-2299286-1
4.5 REF.	4.6	3.2 REF.	3.0	2.29-3.30	20-16	2299286-2
3.4 REF.	4.1	2.1 REF.	2.3	1.52-2.79	24-20	2299286-1
DIM D	DIM C	DIM B	DIM A	INSULATION (MM)	WIRE SIZE (AWG)	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 08FEB2017

CHK 08FEB2017

APVD 08FEB2017

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

SCALE 2:1

SHEET 1 OF 1

REV A8

TE Connectivity

NAME POD-LOK 187 STR. ASSY.

SIZE A2

CAGE CODE

DRAWING NO C-2299286

RESTRICTED TO