



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
ES	00		A	REVISED ECR-17-016956	17NOV17	J.J W.H





SIGNAL SECTION
SECTION B-B



POWER SECTION
SECTION A-A



PANEL CUT DIMENSIONS



VIEW S

VIEW T

NOTES

- MATERIAL
HOUSING: THERMO PLASTIC
CONTACT: COPPER ALLOY
- CONTACT FINISH
MATING SIDE: NICKEL PL. ALL OVER GOLD PL.
CT MATING SIDE: NICKEL PL. ALL OVER MATTE TIN PL.
- APPLIED POWER CONTACT P/N

FINISH	AWG	STRIP	LOOSE PIECE
GOLD PL.	#16~20	179321-3	
	#20~24	179322-3	
TIN PL.	#16~20	1-179321-2	
	#20~24	1-179322-2	

- 4 P: NUMBER OF POWER CONTACT (UNLOADED)
S: NUMBER OF SIGNAL CONTACT (PRELOADED)

TOLERANCE UNLESS OTHERWISE SPECIFIED	
10>*	±0.2
30>*>10	±0.25
100>*>30	±0.3
ANGLE	±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.JIANG 05FEB03	tyco Tyco Electronics Corporation Shanghai, P.R.China,200233	
DIMENSIONS: MM		CHK S.YAO 05FEB03		
TOLERANCES UNLESS OTHERWISE SPECIFIED		APVD T.SAKAKI 05FEB03	NAME HYBRID MINI DRAWER CONN. PLUG ASS'Y 4-8(12P) WITH SEQUENTIAL	
0 PLC ± 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH		PRODUCT SPEC 108-60022		
MATERIAL SEE NOTE		APPLICATION SPEC 114-5182 114-5238	SIZE A2	CAGE CODE 00779
SEE NOTE		WEIGHT	DRAWING NO C=292182	RESTRICTED TO -
CUSTOMER DRAWING		SCALE NTS	SHEET 1 OF 1	REV A1