



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
3. PART NUMBERS: SEE SHEET 2 FOR ALL PART NUMBERS.
4. CASSETTE WIRING COMPLIES WITH ANSI/TIA-568-C.0 SEE ANSI/TIA-568-C.0 FOR POLARITY DETAILS AND AN EXAMPLE OF A BASIC LINK.
5. CASSETTE WEIGHT: 6.3oz (178g)



FIBER POSITION FROM LC END TO MPO END													
METHOD A 24F - CASSETTE (AS)													
LC PORT NUMBER	MPO #1						MPO #2						
	1	2	3	4	5	6	7	8	9	10	11	12	
MPO FIBER POSITION	B	A	B	A	B	A	B	A	B	A	B	A	
	1	2	3	4	5	6	7	8	9	10	11	12	
METHOD A FLIPPED 24F - CASSETTE (AF)													
LC PORT NUMBER	MPO #1						MPO #2						
	1	2	3	4	5	6	7	8	9	10	11	12	
MPO FIBER POSITION	B	A	B	A	B	A	B	A	B	A	B	A	
	1	2	3	4	5	6	7	8	9	10	11	12	
METHOD B 24F - CASSETTE (BN)													
LC PORT NUMBER	MPO #1						MPO #2						
	1	2	3	4	5	6	7	8	9	10	11	12	
MPO FIBER POSITION	B	A	B	A	B	A	B	A	B	A	B	A	
	12	11	10	9	8	7	6	5	4	3	2	1	

TITLE

HD FLEX CASSETTE, 12-PORT
 DUPLEX LC TO (2) 12-FIBER MPO

CUSTOMER DRAWING

ITEM REVISION NAME

12F187MG/02

DATASET FILE NAME

12F187MG_DC/02A


UNLESS OTHERWISE SPECIFIED,
 DIMENSIONAL TOLERANCES ARE: IN [mm]

.x ± .1 [2.54]

.xxx ± .005 [.127]

.xx ± .01 [.25]

ANGLES ± 5 °



THIRD ANGLE
 PROJECTION

MATERIAL:

DRAWING NUMBER:


12F187MG-DC

00	09-16-16	SAT	TMSE	EJH	RELEASED TO PRODUCTION	12F187MG-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 2	SIZE
SAT	09-09-16	TMSE	NONE		A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

CASSETTE PART NUMBER	DESCRIPTION
FHC9N-24-10AS	OS2 HD FLEX CASSETTE, 12-PORT DUPLEX LC TO (2) 12-FIBER MPO, METHOD A
FHC9N-24-10AF	OS2 HD FLEX CASSETTE, 12-PORT DUPLEX LC TO (2) 12-FIBER MPO, METHOD A PAIR FLIPPED
FHCX0-24-10AS	OM3 HD FLEX CASSETTE, 12-PORT DUPLEX LC TO (2) 12-FIBER MPO, OPTIMIZED LOSS, METHOD A
FHCX0-24-10AF	OM3 HD FLEX CASSETTE, 12-PORT DUPLEX LC TO (2) 12-FIBER MPO, OPTIMIZED LOSS, METHOD A PAIR FLIPPED
FHCX0-24-10BN	OM3 HD FLEX CASSETTE, 12-PORT DUPLEX LC TO (2) 12-FIBER MPO, OPTIMIZED LOSS, METHOD B
FHCZ0-24-10AS	OM4 HD FLEX CASSETTE, 12-PORT DUPLEX LC TO (2) 12-FIBER MPO, OPTIMIZED LOSS, METHOD A
FHCZ0-24-10AF	OM4 HD FLEX CASSETTE, 12-PORT DUPLEX LC TO (2) 12-FIBER MPO, OPTIMIZED LOSS, METHOD A PAIR FLIPPED
FHCZ0-24-10BN	OM4 HD FLEX CASSETTE, 12-PORT DUPLEX LC TO (2) 12-FIBER MPO, OPTIMIZED LOSS, METHOD B
FHCZA-24-10AS	OM4 HD FLEX CASSETTE, 12-PORT DUPLEX LC TO (2) 12-FIBER MPO, ULTRA LOSS, METHOD A
FHCZA-24-10AF	OM4 HD FLEX CASSETTE, 12-PORT DUPLEX LC TO (2) 12-FIBER MPO, ULTRA LOSS, METHOD A PAIR FLIPPED
FHCZA-24-10BN	OM4 HD FLEX CASSETTE, 12-PORT DUPLEX LC TO (2) 12-FIBER MPO, ULTRA LOSS, METHOD B

								TITLE HD FLEX CASSETTE, 12-PORT DUPLEX LC TO (2) 12-FIBER MPO CUSTOMER DRAWING				
								ITEM REVISION NAME 12F187MG/02				
								DATASET FILE NAME 12F187MG_DC/02A				
								UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .1 [2.54] .XXX ± .005 [.127] .XX ± .01 [.25] ANGLES ± 5 °				
								 THIRD ANGLE PROJECTION			MATERIAL:	
00	09-16-16	SAT	TMSE	EJH	SEE SHEET 1 FOR REVISIONS	12F187MG-DC					DRAWING NUMBER: 12F187MG-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 2 OF 2	SIZE A
							SAT	09-09-16	TMSE	NONE		