



Carling Technologies®  
/// NOW PART OF



Littelfuse®

# LD-Series

Electronic Dimmer Controls

**PRODUCT WEBPAGE**

*request sample, configure part*



The LD-Series represents a dynamic breakthrough in dashboard technology, with its programmable circuitry, superior design, and unparalleled performance that affords seamless integration into most any dash panel. A variety of options, along with superior performance, functionality, and aesthetics assure compliance with the most stringent customer requirements.

**1**

Pole

**2-10**

Amps

**12-24**

VDC

## Typical Applications

- On/Off-Highway Equipment
- Agricultural Equipment
- Construction Equipment

# Tech Specs

## Electrical

|                     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Contact Rating      | 9-16VDC, 2-10Amp.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| Terminals           | 6.3mm (0.250" TAB)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Contacts            | solid-state load switching                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| Output              | PWM 200 Hz.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| EMI/EMC             | SAE J1113 and SAE J1455<br>Conducted Transient Emissions<br>RF Conducted Emissions<br>Conducted Susceptibility:<br>Test pulse #1<br>Test pulse #2<br>Test pulse #3a, #3b<br>Load Dump: Test Pulse #5<br>Power lead Disturbance<br>(Power Dips)<br>AF Conducted Immunity<br>Direct RF Injection (DRFI)<br>Abnormal Vehicle Operating<br>Conditions<br>RF Radiated Emissions<br>Radiated Immunity-Absorber<br>Lined Chamber<br>Electrostatic Discharge:<br>Shipping / handling Electrostatic<br>Discharge: Human Static<br>Discharge |
| Dielectric Strength | 000V @ 60 Hz was applied for<br>each unit for 1 minute                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Reverse Polarity    | 24VDC for 5 minutes                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |


## Physical

|                 |                                            |
|-----------------|--------------------------------------------|
| Function        | Incremental for continuous<br>dimming      |
| Operation       | Momentary                                  |
| Lighted         | LED's internally dimmed                    |
| Base            | PBT Polyester V-0 flammability             |
| Rocker          | Polycarbonate or Nylon 6/6<br>Glass filled |
| Bracket         | PBT Polyester V-0 flammability             |
| Connector       | Nylon 6/6 toughened                        |
| Actuation Force | 300 gm ± 50 gm                             |
| Weight          | 52 grams                                   |

## Environmental

|                     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
|---------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Operating Temp.     | -40°C to + 85°C                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| Vibration           | Resonance Search<br>Individual resonance<br>searches were conducted<br>with vibration applied along<br>each of the three mutually<br>perpendicular axes.<br>24-50 Hz 0.40DA<br>50-2000 Hz ± 10 G's peak<br>Random Vibration<br>The random vibration endurance<br>test conditions were sequentially<br>conducted in each of the three<br>mutually perpendicular axes, 1hr/<br>axis<br>Freq. (Hz) PSD (G <sup>2</sup> /Hz) 9.36 grms<br>24 Hz 0.06<br>60 Hz 0.50<br>100 Hz 0.025<br>1000 Hz 0.025<br>2000 Hz 0.025<br>During the test, all units were<br>operated at a load current of 2A<br>with 12.5VDC. |
| Salt Spray          | Per Mil-Std 202F, Method 101D, Test<br>Condition A. Duration 96 hrs.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| Dust                | Per Mil-Std 810C, Method 510.2. Air<br>velocity 300 ± 200 Feet/Min., Test<br>Duration 16 Hr.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Moisture Resistance | Per Mil-Std 202F, Method 106E.<br>Test Criteria-pre and post test<br>operation of switch.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |

## Mounting Specifications



MOUNTING HOLE

**Panel Thickness Range**  
Acceptable Panel Thickness  
.030 to .156 (.76mm to 3.96mm)  
Recommended:  
.030, .062, .093, .125 and .156

|                    |                                  |   |   |   |   |   |   |   |   |    |    |    |    |
|--------------------|----------------------------------|---|---|---|---|---|---|---|---|----|----|----|----|
| Sample Part Number | LD 3 5 1 C C 1 - 3 A A FE - 1 FC |   |   |   |   |   |   |   |   |    |    |    |    |
| Selection          | 1                                | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 |

## Selection

**LD** Electronic Dimmer Control

|          |               |          |              |
|----------|---------------|----------|--------------|
| <b>1</b> | 4A, 12 volts  | <b>A</b> | 2A, 24 volts |
| <b>2</b> | 7A, 12 volts  | <b>C</b> | 5A, 24 volts |
| <b>3</b> | 10A, 12 volts |          |              |

|          |                        |          |                       |
|----------|------------------------|----------|-----------------------|
| <b>1</b> | 30 - 100% 8 positions  | <b>A</b> | 0 - 100% 11 positions |
| <b>5</b> | 10 - 100% 10 positions |          |                       |

1 .230 TABS (5.84 mm)

|         |          |          |          |
|---------|----------|----------|----------|
| No lamp | <b>S</b> |          |          |
|         | Red      | Amber    | Green    |
| 12V LED | <b>C</b> | <b>N</b> | <b>H</b> |
| 24V LED | <b>D</b> | <b>P</b> | <b>J</b> |


| 1     | 2     | 3    |
|-------|-------|------|
| Black | White | Gray |

|        |              |       |       |      |     |
|--------|--------------|-------|-------|------|-----|
|        | Laser Etched | Black | White | Gray | Red |
| Rocker | 3            | A     | B     | C    | D   |
| Paddle | 4            | J     | K     | M    | N   |

| Z     | No Lens |       |       |     |      |  |                   |
|-------|---------|-------|-------|-----|------|--|-------------------|
| Clear | White   | Amber | Green | Red | Blue |  | Lens Style        |
| 1     | -       | B     | G     | M   | T    |  | Large Transparent |
| -     | 7       | C     | H     | N   | U    |  | Large Translucent |
| 3     | -       | D     | J     | P   | V    |  | Bar Transparent   |
| -     | 9       | E     | K     | R   | W    |  | Bar Translucent   |
| 5     | A       | -     | -     | -   | -    |  | Laser Etch        |

00 No legend      FC Dim      FE Bright  
For legend options, visit us at [carlingtech.com](http://carlingtech.com)

0 No legend  
1 vertical (lamp 1 on top)  
2 horizontal (lamp 1 on right)  
3 vertical (lamp 1 on bottom)




00 No legend FC Dim FE Bright  
For legend options, visit us at [carlingtech.com](http://carlingtech.com)

Notes:  
1 Custom colors are available. Consult factory.

 **Configure Complete Part Number >**

## inches [millimeters]



## Authorized Sales Representatives and Distributors

Click on a region of the map below to find your local representatives and distributors or visit [www.carlingtech.com/findarep](http://www.carlingtech.com/findarep).



## About Carling

Founded in 1920, Carling Technologies is a leading manufacturer of electrical and electronic switches and assemblies, circuit breakers, electronic controls, power distribution units, and multiplexed power distribution systems. With six ISO9001 and IATF16949 registered manufacturing facilities and technical sales offices worldwide, Carling Technologies Sales, Service and Engineering teams do much more than manufacture electrical components, they engineer powerful solutions! To learn more about Carling please visit [www.carlingtech.com/company-profile](http://www.carlingtech.com/company-profile).

To view all of Carling's environmental, quality, health & safety certifications please visit [www.carlingtech.com/environmental-certifications](http://www.carlingtech.com/environmental-certifications).