

## Coaxial Cable Connector 11\_N-50-5-18/103\_N

### Description

Straight cable plug

Interface standards

IEC 61169-16\_MIL-STD-348A/304\_CECC 22210



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

#### Mechanical Data

Centre contact	soldered
Outer contact	soldered
Weight	0.0219 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Brass	Silver Plating
Body	Brass	Silver Plating
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Brass	SUCOPRO (R) Plating
Gasket	VMQ (Silicone rubber)	

### Related Documents

Outline drawing	DOU-00061619
Assembly instruction	DOC-0000215552

### Ordering Information

Bulk 100 pcs package	11_N-50-5-18/103_NH
----------------------	---------------------

### Additional Information

Suitable cables	EZ_250_TP_M17, SUCOFOR_250-01_FEP
-----------------	-----------------------------------