


8.13
[0.320 in]



SWITCH FUNCTION		
POS. 1	POS. 1	POS. 1
		
ON	NONE	ON
2-3	OPEN	2-1



CIRCUIT: SPST

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. PLATING MATERIAL: SILVER
5. RATING: 5 AMPS W/RESISTIVE LOAD @ 120VAC OR 28VDC
2 AMPS W/RESISTIVE LOAD @ 250VAC
6. ELECTRIC LIFE: 40,000 make-and-break cycles
at full load.
7. INSULATION RESISTANCE: 1,000 Mega-ohm min.
8. DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
9. OPERATING TEMP.: -30°C to 85°C
10. ▲ DENOTES CRITICAL PARAMETER.
11. 2002/95/EC (ROHS) COMPLIANT



ISOMETRIC

11. 10627957EC (ROHS) COMPLIANT				
C	15790	EDIT TOGGLE DIA.	2/17/06	PH
B	15517	ADD ROHS NOTE	11/9/05	PH
A	14161	RELEASED FOR PRODUCTION	7/12/04	AR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

E-SWITCH®

TITLE 100SP1T4B1VS2QE

SCALE 2:1

DATE 7/12/2004

DR	
AR	

DWG	T111039
-----	---------

REV
C