




Cable Assemblies > Data Bus Components > Data Bus Terminators



Contact Type: **Socket**

Impedance: **3000 Ω**

Data Bus Connector Style: **Threaded**

Data Bus Connector Type: **Plug**

Features

Product Type Features

Data Bus Connector Style	Threaded
Data Bus Connector Type	Plug

Electrical Characteristics

Impedance	3000 Ω
-----------	--------

Contact Features

Contact Type	Socket
--------------	--------

Termination Features

Termination Method to Wire & Cable	Solder
------------------------------------	--------

Usage Conditions

Operating Temperature (Max)	125 °C
-----------------------------	--------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Pb (37% in Solder)



Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 750984-004

[10612-24-9](#)

Customers Also Bought



TE Part #1-1734829-1

[1.25 WTB HDR DIP, 11 POS](#)




TE Part #226781-3

[ARINC SIZE 15 SOCKET](#)



TE Part #1-1744418-6

[16 POS EP 2.5 HDR, GLOW WIRE](#)



TE Part #1776253-8


[8P TB ,180deg,RT,3.5mm, Blue,w /interlock](#)



TE Part #1969591-9
HSG, REC, PANEL MOUNT, GWT,
SINGLE ROW, EP2.5




TE Part #2007815-3
IMP100S, H, V4P10C, RG, LEW39, 5.5



TE Part #63020-1
BRUSH TERMINAL 24-20 AWG BR



TE Part #5-6609074-1
60DCB10B J0=F7955



TE Part #387239-000
44A1112-24-9-9



TE Part #3-641523-4
04P MTA156 POST CON ASSY LF

Documents

Product Drawings

D-621-0407

English

D-621-0407

English

Datasheets & Catalog Pages

Data Bus Components Brochure

English

Product Specifications

Product Specification

English

Product Specification

English