






SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40 $^{\circ}$ to+105 $^{\circ}$
Contact Material: Brass
Standard: PA6T
Insrlator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240 $^{\circ}$ C for30-60seconds
(260 $^{\circ}$ C for 5 seconds)


P/N	PIN	DIM.A	DIM.B
FH2.0-01-01PZS	2*1	0.00	2.00
FH2.0-01-02PZS	2*2	2.00	4.00
FH2.0-01-03PZS	2*3	4.00	6.00
FH2.0-01-04PZS	2*4	6.00	8.00
FH2.0-01-05PZS	2*5	8.00	10.00
FH2.0-01-06PZS	2*6	10.00	12.00
FH2.0-01-07PZS	2*7	12.00	14.00
FH2.0-01-08PZS	2*8	14.00	16.00
FH2.0-01-09PZS	2*9	16.00	18.00
.....			
FH2.0-01-40PZS	2*40	(PIN-1)x2.0	(PIN)x2.0



PART NUMBER DESCRIPTION:

FH2.0-01-NPZS

(D=单排;S=双排)
(Z=直脚;W=弯脚)
(PIN数量;01.....40PIN)
(排针开关)



MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:2.0FH H4.3 2xPin 180度 W4.5 U型 PC2.8 6T
			PAR FH2.0-01-NPZS
DECIMALS:	ANGLES:		DWN
X.±0.30	X $^{\circ}$ ±5 $^{\circ}$		CHKD
X.X±0.20	X.X $^{\circ}$ ±1 $^{\circ}$	CUSTOMER COPY	APVD
X.XX±0.10	X.XX $^{\circ}$ ±0.5 $^{\circ}$		SCALE N:A
		SIZE:A4	UNIT:MM
		SHEET:1F1	REV:A