




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		B2	REVISED PER ECO-11-004835	11MAR11	RK	HMR

- THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.
- DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- MATERIAL: HOUSING AND COVER - POLYPHENYLENE OXIDE.
CABLE CLAMP - POLYESTER MOLDING COMPOUND.
TERMINAL - HIGH STRENGTH COPPER ALLOY PLATED WITH $0.76\mu\text{m}$ [.000030] MIN GOLD OR GOLD FLASH OVER PALLADIUM NICKEL PLATE, $0.76\mu\text{m}$ [.000030] MIN TOTAL ON MATING SURFACE, OVER $1.27\mu\text{m}$ [.000050] MIN NICKEL UNDERPLATE.
HARDWARE - ZINC PLATED STEEL.
DUST COVER - POLYETHYLENE MOLDING COMPOUND.
- THIS KIT SHIPPED NOT ASSEMBLED.
- WIRE SIZE: 24 & 26 AWG SOLID & 24 AWG STRAND COPPER CONDUCTORS. MAXIMUM INSULATION DIAMETER OF 1.15[.045] IS ACCEPTABLE FOR MOST APPLICATIONS.
- CORING MAY OR MAY NOT APPEAR AND IS AT THE DISCRETION OF AMP INCORPORATED.
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

BULK PACKED	$\phi 7.62-8.26$ [$\phi .300-.325$]	YES	BLACK	$\Delta 6-5229913-7$
	$\phi 8.89-10.80$ [$\phi .350-.425$]	YES	GRAY	$\Delta 6-5229913-4$
		YES	BLACK	$6-5229913-3$
		NO	BLACK	$6-5229913-1$
POLY BAGGED	$\phi 10.80-12.70$ [$\phi .425-.500$]	YES	BLACK	$3-5229913-1$
		NO	BLACK	$2-5229913-1$
	$\phi 8.89-10.80$ [$\phi .350-.425$]	YES	GRAY	$\Delta 1-5229913-4$
		YES	BLACK	$1-5229913-1$
		NO	GRAY	$5229913-4$
PACKAGING	CABLE RANGE	DUST COVER	COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	23SEP05	TE Connectivity			
		CHK	23SEP05				
		APVD	23SEP05	NAME RECEPTACLE KIT, 50 POSITION, B-SLOT, SCREW LOCK, TAPERED COVER, CHAMP-LOK			
		PRODUCT SPEC					
		APPLICATION SPEC		SIZE		CAGE CODE	DRAWING NO
				A2		00779	C=5229913
		WEIGHT	-	SCALE		SHEET	REV
				2:1		1 of 1	B2
		CUSTOMER DRAWING					