

Data sheet

3RA2225-4BB26-0AK6

FUSELESS MOTOR STARTER REVERSING OPERATION 600V AC SZ S0 14-20A 110/120V AC 50/60HZ SCREW CONNECTION FOR 35 MM RAIL-MOUNTING TYPE OF COORDINATION 2 IQ = 50 KA ALSO FULFILLS TYPE OF COORDINATION 1 1NO+1NC (MSP) 1NO+1NC (PER CONTACTOR)

| | |
|--|-------------------------------|
| product brand name | SIRIUS |
| product designation | non-fused motor starter 3RA2 |
| design of the product | reversing starter |
| manufacturer's article number | |
| • of the supplied contactor | 3RT2026-1AK60 |
| • of the supplied circuit-breakers | 3RV2021-4BA15 |
| • of the supplied RH assembly kit | 3RA2923-1BB1 |
| • of the supplied busbar adapter | 3RA2922-1AA00 |
| • of the supplied link module | 3RA2921-1AA00 |
| • of the supplied standard mounting rail adapter | 3RA2922-1AA00 |

| General technical data | |
|---|------------|
| size of the circuit-breaker | S0 |
| size of load feeder | S0 |
| product extension auxiliary switch | Yes |
| insulation voltage with degree of pollution 3 at AC rated value | 690 V |
| degree of pollution | 3 |
| surge voltage resistance rated value | 6 kV |
| shock resistance according to IEC 60068-2-27 | 6g / 11 ms |
| mechanical service life (operating cycles) of contactor typical | 10 000 000 |
| type of assignment | 2 |
| Substance Prohibition (Date) | 03/01/2017 |
| Weight | 1.45 kg |

| Ambient conditions | |
|---------------------|----------------|
| ambient temperature | |
| • during operation | -20 ... +60 °C |
| • during storage | -50 ... +80 °C |
| • during transport | -55 ... +80 °C |

| Main circuit | |
|---|-------------------|
| number of poles for main current circuit | 3 |
| design of the switching contact | electromechanical |
| adjustable current response value current of the current-dependent overload release | 14 ... 20 A |
| operating voltage | |
| • rated value | 690 V |
| • at AC-3 rated value maximum | 690 V |
| operating frequency rated value | 50 ... 60 Hz |
| operational current at AC-3 at 400 V rated value | 15.5 A |
| operating power at AC-3 | |
| • at 400 V rated value | 7 500 W |
| • at 500 V rated value | 11 000 W |

| Control circuit/ Control | |
|---|--------------|
| control supply voltage at AC | |
| • at 50 Hz rated value | 110 V |
| • at 50 Hz rated value | 88 ... 121 V |
| • at 60 Hz rated value | 120 V |
| • at 60 Hz rated value | 96 ... 132 V |
| apparent holding power of magnet coil at AC | 9.4 VA |
| inductive power factor with the holding power of the coil | 0.28 |

| Auxiliary circuit | |
|--|---|
| number of NC contacts for auxiliary contacts | 3 |

| | |
|--|--|
| number of NO contacts for auxiliary contacts | 3 |
| Protective and monitoring functions | |
| trip class | CLASS 10 |
| design of the overload release | thermal (bimetallic) |
| response value current of instantaneous short-circuit trip unit | 260 A |
| UL/CSA ratings | |
| full-load current (FLA) for 3-phase AC motor | |
| • at 480 V rated value | 15.2 A |
| • at 600 V rated value | 17.8 A |
| yielded mechanical performance [hp] | |
| • for single-phase AC motor | |
| — at 110/120 V rated value | 1.5 hp |
| — at 230 V rated value | 3 hp |
| • for 3-phase AC motor | |
| — at 200/208 V rated value | 5 hp |
| — at 220/230 V rated value | 5 hp |
| — at 460/480 V rated value | 10 hp |
| — at 575/600 V rated value | 15 hp |
| Short-circuit protection | |
| product function short circuit protection | Yes |
| design of the short-circuit trip | magnetic |
| conditional short-circuit current (Iq) | |
| • at 400 V according to IEC 60947-4-1 rated value | 153 000 A |
| Installation/ mounting/ dimensions | |
| mounting position | vertical |
| fastening method | snap-on fastening on 35 mm DIN rail |
| height | 265 mm |
| width | 90 mm |
| depth | 120 mm |
| required spacing | |
| • for grounded parts | |
| — forwards | 10 mm |
| — backwards | 0 mm |
| — upwards | 30 mm |
| — at the side | 9 mm |
| — downwards | 10 mm |
| • for live parts | |
| — forwards | 10 mm |
| — backwards | 0 mm |
| — upwards | 30 mm |
| — downwards | 10 mm |
| — at the side | 9 mm |
| Connections/ Terminals | |
| type of electrical connection for main current circuit | screw-type terminals |
| type of connectable conductor cross-sections for main contacts stranded | 1 ... 10 mm ² , 2x (2.5 ... 6 mm ²) |
| connectable conductor cross-section for main contacts finely stranded with core end processing | 1 ... 6 mm ² |
| Safety related data | |
| proportion of dangerous failures with high demand rate according to SN 31920 | 73 % |
| B10 value with high demand rate according to SN 31920 | 1 000 000 |
| Electrical Safety | |
| protection class IP on the front according to IEC 60529 | IP20 |
| touch protection on the front according to IEC 60529 | finger-safe, for vertical contact from the front |
| Approvals Certificates | |
| General Product Approval | For use in hazardous locations |



[Confirmation](#)



Test Certificates

Marine / Shipping

[Special Test Certificate](#)

[Type Test Certificates/Test Report](#)



Marine / Shipping

other

Railway

Environment



[Confirmation](#)

[Special Test Certificate](#)

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2225-4BB26-0AK6>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2225-4BB26-0AK6>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RA2225-4BB26-0AK6>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2225-4BB26-0AK6&lang=en

Characteristic: Tripping characteristics, I^tt, Let-through current

<https://support.industry.siemens.com/cs/ww/en/ps/3RA2225-4BB26-0AK6/char>

Further characteristics (e.g. electrical endurance, switching frequency)

<http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2225-4BB26-0AK6&objecttype=14&gridview=view1>

last modified:

11/21/2022