








PCB MOUNTING



CIRCUIT: SPST ▲

NOTES:

1. ALL DIMENSIONS IN mm [INCH].
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 50mA @ 12VDC
- ▲ 5. OPERATING FORCE: 100 $\pm$ 50 gf
6. TRAVEL: 0.25 +0.20/-0.10 mm
7. CONTACT RESISTANCE: 100 MILLI-OHMS MAX. (INITIAL)
8. MECHANICAL/ELECTRICAL LIFE: 100,000 CYCLES MIN.
- ▲ 9. CONTACT MATERIAL: SILVER
10. ▲ DENOTES CRITICAL PARAMETER.
11. OPERATING TEMP: -40°C TO 85°C

BLACK CAP
1RBLK (Q800300)SWITCH
TL1105JAF100Q
(P010209)

D	24553	REMOVE STEP IN HOUSING, CHANGE TEMP	10/30/20	JM
C	23224	Correct switch p/n to P010209	2/16/18	MW
B	20600	AD TERMINAL NUMBERS, 12.45 WAS 11.53	05/10/12	DRG
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



E-SWITCH®

TITLE TL1105JAF100Q1RBLK

SCALE
4:1DATE
9/20/2006DR
MWDWG
XP0178AREV
D