


**SERIES**


**CM7560R**  
**CM7560**



**PC Mount Common Mode Choke**



Actual Size



**Physical Parameters**

|   | Inches            | Millimeters      |
|---|-------------------|------------------|
| A | 0.860 ± 0.025     | 21.8 ± 0.64      |
| B | 1.070 ± 0.050     | 27.2 ± 1.27      |
| C | 0.830 ± 0.030     | 21.1 ± 0.76      |
| D | 1.060 (Ref. only) | 26.9 (Ref. only) |
| E | 0.040 ± 0.025     | 1.0 ± 0.64       |
| F | 0.025 Sq. (Typ.)  | 0.64 Sq. (Typ.)  |
| G | 0.400 ± 0.010     | 10.2 ± 0.3       |
| H | 0.175 ± 0.015     | 4.4 ± 0.38       |
| J | 1.03 (Ref. only)  | 26.2 (Ref. only) |
| K | 0.400 ± 0.010     | 10.2 ± 0.3       |
| L | 0.630 ± 0.010     | 16.0 ± 0.3       |

**Operating Temperature Range** -55°C to +125°C

**Current Rating at 85°C Ambient** 40°C Rise

**Mechanical Configuration** Tape wrapped winding sections; varnish impregnated assembly

**Notes** 1) Inductance in table is for either L1 or L2.  
2) Leakage Inductance tested at L1 with L2 shorted or at L2 with L1 shorted. 3) Windings balanced within 1%.

DASH NUMBER\*

L (μH) L1 or L2  
@ 1 kHz ±25%

DC RESISTANCE  
MAXIMUM (OHMS)

CURRENT RATING  
MAXIMUM (AMPS)

LEAKAGE INDUCTANCE  
MAXIMUM (μH)

**SERIES CM7560 FERRITE CORE**

|      |        |       |      |      |
|------|--------|-------|------|------|
| -563 | 56     | 0.013 | 5.5  | 3.5  |
| -683 | 68     | 0.013 | 5.5  | 3.5  |
| -823 | 82     | 0.013 | 5.5  | 3.5  |
| -104 | 100    | 0.013 | 5.5  | 3.5  |
| -124 | 120    | 0.015 | 5.5  | 4.5  |
| -154 | 150    | 0.015 | 5.5  | 6.0  |
| -184 | 180    | 0.019 | 4.5  | 7.0  |
| -224 | 220    | 0.020 | 4.5  | 7.5  |
| -274 | 270    | 0.025 | 4.5  | 9.0  |
| -334 | 330    | 0.025 | 3.5  | 12   |
| -474 | 470    | 0.030 | 3.5  | 14   |
| -564 | 560    | 0.035 | 3.5  | 18   |
| -684 | 680    | 0.040 | 3.5  | 20   |
| -824 | 820    | 0.060 | 2.8  | 24   |
| -105 | 1000   | 0.065 | 2.8  | 30   |
| -125 | 1200   | 0.095 | 2.2  | 35   |
| -155 | 1500   | 0.115 | 1.7  | 40   |
| -185 | 1800   | 0.125 | 1.7  | 45   |
| -225 | 2200   | 0.170 | 1.4  | 55   |
| -275 | 2700   | 0.180 | 1.4  | 75   |
| -335 | 3300   | 0.320 | 1.1  | 90   |
| -395 | 3900   | 0.400 | 1.1  | 100  |
| -475 | 4700   | 0.450 | 0.88 | 130  |
| -565 | 5600   | 0.500 | 0.88 | 175  |
| -685 | 6800   | 0.600 | 0.88 | 220  |
| -825 | 8200   | 0.750 | 0.88 | 230  |
| -106 | 10000  | 0.800 | 0.70 | 250  |
| -126 | 12000  | 0.900 | 0.70 | 300  |
| -156 | 15000  | 1.00  | 0.70 | 350  |
| -186 | 18000  | 1.30  | 0.55 | 425  |
| -226 | 22000  | 1.50  | 0.55 | 475  |
| -276 | 27000  | 1.80  | 0.44 | 550  |
| -336 | 33000  | 2.20  | 0.44 | 650  |
| -396 | 39000  | 2.60  | 0.44 | 800  |
| -476 | 47000  | 3.00  | 0.44 | 900  |
| -566 | 56000  | 4.00  | 0.35 | 1100 |
| -686 | 68000  | 5.00  | 0.27 | 1300 |
| -826 | 82000  | 5.50  | 0.27 | 1800 |
| -107 | 100000 | 6.40  | 0.27 | 2100 |
| -127 | 120000 | 7.80  | 0.22 | 2600 |
| -157 | 150000 | 9.00  | 0.22 | 3000 |

\*Complete part # must include series # PLUS the dash #

**Marking** DELEVAN; part number.

Example: CM7560-563

DELEVAN

CM7560-563

**Packaging** Bulk only