



— , —

ALL RIGHTS RESERVED.

P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	REVISE PER ECO-18-001534	30JAN2018	LL	SH



RECOMMENDED PCB LAYOUT
RECOMMENDED PCB THICKNESS: 1.6mm
TOLERANCE: ± 0.05 (TOP VIEW)

- 1.1 MJ HOUSING: PBT, WITH 30% GF, UL94 V-0,
COLOR: SEE TABLE.
- 1.2 MJ CONTACTS: PHOSPHOR BRONZE.
- 1.3 MJ SHIELD: BRASS.
- 1.4 USB HOUSING: PBT, UL94 V-0, COLOR: SEE TABLE.
- 1.5 USB CONTACTS: BRASS.
- 1.6 USB SHIELD: SPCC.

2.1 MJ CONTACTS: SELECTIVE GOLD PLATED (SEE TABLE)
ON CONTACT AREA,
GOLD FLASH ON SOLDER TAILS,
1.27um [50u"] MIN. NICKEL UNDERPLATED
OVERALL.

2.2 MJ SHIELD: 0.508um [20u"] MIN. NICKEL PLATED.


2.3 USB CONTACT: SELECTIVE GOLD PLATED (SEE TABLE) ON
2.54um [100u"] MIN. BRIGHT-TIN PLATED
1.27um [50u"] MIN. NICKEL UNDERPLATED

2.4 USB SHIELD: 2.032um [80u"] MIN. NICKEL PLATED.

3. HOT TIN DIP ON SHELL'S LEGS.

4. WAVE SOLDER CAPABLE TO 265°C PER TE CONNECTIVITY SPEC. 109-202, CONDITION B.


5. RJ45 CAVITY CONFIRMS TO FCC RULES AND REGULATIONS PART 68, SUBPART F.



OBSOLETE	12.61	WITHOUT HTD	2.8	BLACK	0.762um [30u"]	3-1775855-1
				COOL GRAY 1C	GOLD FLASH	2-1775855-2
				BLACK	GOLD FLASH	2-1775855-1
	12.61	WITH HTD 	2.6	BLACK	0.762um [30u"]	1-1775855-1
				BLACK	GOLD FLASH	1775855-3
			2.8	GOOL GRAY 1C	GOLD FLASH	1775855-2
				BLACK	GOLD FLASH	1775855-1
	WEIGHT (gram)	HOT TIN DIP ON SHELL'S LEGS	DIM A	HOUSING COLOR	MIN. GOLD THICKNESS	PART NUMBER

CUSTOMER DRAWING:

TOLERANCES UNLESS
OTHERWISE SPECIFIED:



MATERIAL	SEE TABLE
----------	-----------

0	PLC
1	PLC
2	PLC
3	PLC
4	PLC
ANGLES	
FINISH	

$\pm -$
$\pm 0.$
$\pm 0.$
$\pm 0.$
$\pm -$

WEIGHT —

CUSTOMER DRAWING



TE Connectivity Ltd.

MODULAR JACK, RJ45, STACKED OVER,
USB CONN., DIP TYPE


A3 00779 C-1775855	—
--------------------	---


SCALE	1:1	SHEET	1 OF 5	REV	E
-------	-----	-------	--------	-----	---

—, —


ALL RIGHTS RESERVED.

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—





P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. HSING 12JUN2009		TE Connectivity Ltd.							
		CHK S. CHIEN 12JUN2009									
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± 0.3 2 PLC ± 0.2 3 PLC ± 0.15 4 PLC ± — ANGLES ± 3°		APVD W. KODAMA 12JUN2009		NAME MODULAR JACK, RJ45, STACKED OVER, USB CONN., DIP TYPE —					
				PRODUCT SPEC 108-57802							
				APPLICATION SPEC —							
				WEIGHT —							
				CUSTOMER DRAWING							
MATERIAL SEE TABEL		FINISH —		SIZE A3		CAGE CODE 00779		DRAWING NO C-1775855		RESTRICTED TO —	
						SCALE 1:1		SHEET 4 OF 5		REV F	

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


- , - .

© COPYRIGHT — TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



- NOTES:
1. MATERIAL:
TRAY: PVC.
BOX: CORRUGATED FIBER.
 2. DIMENSION: SEE DRAWING
 3. QUANTITY: SEE TABLE
 4. WEIGHT: SEE TABLE

7.85KG	6.45KG	50	10	500	6-1775855-3
					6-1775855-1
7.75KG	6.35KG				5-1775855-1
7.96KG	6.56KG				4-1775855-2
					4-1775855-1
7.71KG	6.31KG				3-1775855-1
					2-1775855-2
					2-1775855-1
					1-1775855-1
					1775855-3
					1775855-2
					1775855-1
GROSS WEIGHT	NET WEIGHT	PCS/ TRAY	TRAY/ BOX	PCS/ BOX	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. HSING 12JUN2009	TE Connectivity Ltd.		
		CHK S. CHIEN 12JUN2009			
		APVD W. KODAMA 12JUN2009	NAME MODULAR JACK, RJ45, STACKED OVER, USB CONN., DIP TYPE		
		PRODUCT SPEC 108-57802			
		APPLICATION SPEC —	SIZE A3		
		WEIGHT —			
		CUSTOMER DRAWING	CAGE CODE 00779		
			DRAWING NO 1775855		
			RESTRICTED TO —		
			SCALE 1:1		
			SHEET 5 of 5		
			REV E		