

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

NOV ,2001.

© COPYRIGHT 2009 By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

E3

ECR-10-026537

27JUN11

KK

HMR

NOTE:

1

MATERIAL :

HOUSING : NYLON 66 OR EQUIVALENT, UL94V-0, BLACK COLOUR.

CONTACT : COPPER ALLOY

2

FINISH:

CONTACT : GOLD PLATED (SEE TABLE) ON CONTACT AREA

80μ" MIN. TIN PLATED ON SOLDER TAIL,

50μ" MIN. NICKEL UNDERPLATED ALL OVER.


3. APPLICATION :

SOLDERTAIL LENGTH 2.6 FOR PCB THICKNESS 1.6±0.1


1.2 FOR PCB THICKNESS 0.3 MAX.

4. KEYING POS. : HOUSING CAVITY MOLDED SHUT



5. QUALIFICATION TEST REPORT: 501-57197




POSITION 1 MARK



2.0±0.05

POSITION NUMBERS FOR REFERENCE ONLY
AND DO NOT APPEAR ON PARTØ0.75±0.05
TYP.

RECOMMENDED PCB LAYOUT



OBSOLETE	30u"	</
----------	------	--

4

3

2

1

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

NOV ,2001.

© COPYRIGHT 2009 By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

-

SEE SHEET 1

-

-

-

CONNECTOR

BOX

314mm(L)X128mm(W)X11mm(H)

CORRUGATED PAPER

309mm(L)X125mm(W)X0.2mm(H)

OUTER CARTON

340mm(L)X288mm(W)X316(H)

TAPE

INNER CARTON

320mm(L)X138mm(W)X144mm(H)

OBSOLETE		5040	1260	105	40	9-	-9
		4320	1080	90	50	9-	-8
OBSOLETE		4320	1080	90	48	9-	-7
OBSOLETE		4320	1080	90	46	9-	-6
OBSOLETE		4320	1080	90	44	9-	-5
OBSOLETE		5040	1260	105	42	9-	-4
		5040	1260	105	40	9-	-3
OBSOLETE		5040	1260	105	38	9-	-2
OBSOLETE		5760	1440	120	36	9-	-1
OBSOLETE		5760	1440	120	34	9	0
OBSOLETE		6480	1620	135	32	8-	-9
		7200	1800	150	30	8-	-8
OBSOLETE	2.6±0.1	7200	1800	150	28	8-	-7
OBSOLETE		7920	1980	165	26	8	-6
OBSOLETE		8640	2160	180	24	8-	-5
OBSOLETE		9360	2340	195	22	8-	-4
		10080	2520	210	20	8-	-3
OBSOLETE		11520	2880	240	18	8-	-2
OBSOLETE		12960	3240	270	16	8-	-1
OBSOLETE		15120	3780	315	14	8-	0
		17280	4320	360	12	7-	-9
		20880	5220	435	10	7-	-8
OBSOLETE		26640	6660	555	8	7-	-7
		35280	8820	735	6	7-	-6
OBSOLETE		51840	12960	1080	4	7	-5
		4320	1080	90	50	7-	-4
		4320	1080	90	48	7-	-3
		4320	1080	90	46	7-	-2
		4320	1080	90	44	7-	-1
		5040	1260	105	42	7-	0
		5040	1260	105	40	6-	-9
		5040	1260	105	38	6-	-8
		5760	1440	120	36	6-	-7
		5760	1440	120	34	6-	-6
		6480	1620	135	32	6-	-5
		7200	1800	150	30	6-	-4
		7200	1800	150	28	6-	-3
		7920	1980	165	26	6-	-2
		8640	2160	180	24	6-	-1
		9360	2340	195	22	6-	0
		10080	2520	210	20	5-	-9
		11520	2880	240	18	5-	-8
		12960	3240	270	16	5-	-7
		15120	3780	315	14	5-	-6
		17280	4320	360	12	5-	-5
		20880	5220	435	10	5-	-4
		26640	6660	555	8	5-	-3
		35280	8820	735	6	5-	-2
OBSOLETE		51840	12960	1080	4	5	-1
	"L"	Pcs/Carton	Pcs/Inner Carton	Pcs/BOX	POS.	PART NUMBER	

OBSOLETE		5040	1260	105	40	4-	-9
		4320	1080	90	50	4-	-8
OBSOLETE		4320	1080	90	48	4-	-7
OBSOLETE		4320	1080	90	46	4-	-6
		4320	1080	90	44	4-	-5
OBSOLETE		5040	1260	105	42	4	-4
		5040	1260	105	40	4-	-3
OBSOLETE		5040	1260	105	38	4-	-2
OBSOLETE		5760	1440	120	36	4-	-1
OBSOLETE		5760	1440	120	34	4	0
OBSOLETE		6480	1620	135	32	3-	-9
OBSOLETE		7200	1800	150	30	3-	-8
OBSOLETE	2.6±0.1	7200	1800	150	28	3-	-7
		7920	1980	165	26	3-	-6
OBSOLETE		8640	2160	180	24	3-	-5
OBSOLETE		9360	2340	195	22	3-	-4
		10080	2520	210	20	3-	-3
OBSOLETE		11520	2880	240	18	3-	-2
OBSOLETE		12960	3240	270	16	3-	-1
OBSOLETE		15120	3780	315	14	3-	0
		17280	4320	360	12	2-	-9
		20880	5220	435	10	2-	-8
OBSOLETE		26640	6660	555	8	2-	-7
		35280	8820	735	6	2-	-6
OBSOLETE		51840	12960	1080	4	2	-5
		4320	1080	90	50	2-	-4
		4320	1080	90	48	2-	-3
		4320	1080	90	46	2-	-2
		4320	1080	90	44	2-	-1
		5040	1260	105	42	2-	0
		5040	1260	105	40	1-	-9
		5040	1260	105	38	1-	-8
		5760	1440	120	36	1-	-7
		5760	1440	120	34	1-	-6
		6480	1620	135	32	1-	-5
		7200	1800	150	30	1-	-4
		7200	1800	150	28	1-	-3
		7920	1980	165	26	1-	-2
		8640	2160	180	24	1-	-1
		9360	2340	195	22	1-	0
		10080	2520	210	20		-9
		11520	2880	240	18		-8
		12960	3240	270	16		-7
		15120	3780	315	14		-6
		17280	4320	360	12		-5
		20880	5220	435	10		-4
		26640	6660	555	8		-3
		35280	8820	735	6		-2
OBSOLETE		51840	12960	1080	4		-1
	"L"	Pcs/Carton	Pcs/Inner Carton	Pcs/BOX	POS.	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

O.HU

30-NOV-2001

CHK

J.CHENG

30-NOV-2001

APVD

J.WU

30-NOV-2001

PRODUCT SPEC

108-57197

APPLICATION SPEC

—

WEIGHT

—

CUSTOMER DRAWING

SCALE

1:1

SHEET

2 OF 2

REV

E3

STE

TE Connectivity

NAME

AMPMODU 2.0mm PITCH REC

CONN,VERTICAL MOUNT TYPE

SIZE

A3

CAGE CODE

—

DRAWING NO

C-1470209

RESTRICTED TO

—

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —

1 PLC ± 0.15

2 PLC ± 0.10

3 PLC ± 0.05

4 PLC ± —

ANGLES ± 3°

MATERIAL

SEE SHEET 1

FINISH

SEE SHEET 1

1470-19 (3/11)