







712RALP





722RALP



732RALP





721RALP



SCHEMATIC

NOTES:

1. FOR HAND INSERTION USE SPACING 0.130 [3.30]
FOR AUTOMATED INSERTION USE SPACING 0.135 [3.43]
2. HEX NUT AND FLAT WASHER SUPPLIED UNASSEMBLED.
3. MATERIAL:
HOUSING, HEX NUT - COPPER ALLOY, NICKEL PLATED
INSULATOR HOUSING - THERMOPLASTIC
TERMINAL INSULATORS - PHENOLIC
FLAT WASHER - STEEL, NICKEL PLATED
PIN, SPRING, TERMINALS - COPPER ALLOY, SILVER PLATED
4. IT IS RECOMMENDED THAT THE JACK MOUNTING NUT BE
TIGHTENED SNUG BY HAND BEFORE APPLYING A FINAL
TIGHTENING TORQUE OF 8-10 IN-LBS USING HAND TOOLS
ONLY. POWER DRIVER OR IMPACT DRIVERS ARE NOT
RECOMMENDED.
5. THESE PRODUCTS ARE RoHS COMPLIANT



CUSTOMER DRAWING

					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.				
					UNLESS OTHERWISE SPECIFIED	SIZE	WIDTH	MULT	LBS/M
					1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ± 0.02 [0.5] - THREE PLACE DECIMALS ± 0.005 [0.13]				
					FINISH SPEC No.				
A	28408	03-08-22	PC	TJK	FIRST USED ON		SCALE 2:1	MATERIAL SPEC No.	
REV	ECO NUMBER	DATE	BY	APVD	DATE DRAWN	BY	CHKD TJK	APVD TJK	Switchcraft®
					4-16-2020	SRC	05-11-22	05-11-22	SHEET 1 OF 1
REVISIONS					NAME POWER JACKS RIGHT-ANGLE LOW PROFILE, RoHS				
DO NOT SCALE DRAWING					PART No. 7_RALP SERIES				
REV A									