




SIGN	DATE	DESCRIPTION	APPROVER
△	2010.12.20	The design is changed	Chen Bo
△	07/29'11	The torque is changed & Add is the "cULus" mark	Runner
△	07/29'11	The voltage rating is changed from 600V to 300V	Runner
△	07/29'11	The withstanding voltage is changed from 2.2KV to 1.6KV	Runner

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item a Terminal housing : Thermoplastic (UL 94V-0)
- Item b Clamp : Brass, Ni plated.
- Item c Wire guard solder pin (Back single row) : Copper , Tin plated
- Item d Terminal screw: Steel Zinc plating"-slot type

Electrical

- Voltage rating : 300V
- Current rating : 65A
- Wire range :
- Solid wire (AWG) : 6-20
- Stranded wire (AWG) : 6-20
- Torque (LB-In.) : 12.2
- Screw : M4.5
- Wire strip length : 10~11mm
- Withstanding voltage : 1.6KV
- Operating temperature : -40°C+115°C
- Soldering temperature : 250°C+10°C/5 Sec
- Critical dimension:
- Safety Approval:

KP xx 2 1 x 1 xxxx G

02 2 Poles
03 3 Poles
... ..
12 12 Poles

Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)

RoHS
Pb<40,000ppm

0000:"@ "Logo (Standard)
000A:"ANYTEK"Logo
Any special item by
customer request,
please contact sales
department.

Poles	01	02	03	04	05	06	07	08	09	10	11	12
Dim L	10.16	20.32	30.48	40.64	50.80	60.96	71.12	81.28	91.44	101.60	111.76	121.92
Dim B		10.16	20.32	30.48	40.64	50.80	60.96	71.12	81.28	91.44	101.60	111.76
TOL	±0.10	±0.20			±0.30			±0.40				

ANYTEK				CUSTOMER COPY			
				ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD			
TITLE		KP 10.16 Series Back single row (Without cover)					
PART NO.		KPxx21x1xxxxG		DWG NO.		8KP0102	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
			Runner 2011.07.29	Chen Bo 2010.12.20			X. ±0.50
					UNIT: mm		X.X ±0.30
					SCALE: NONE		X.XX ±0.10
					SHEET: 01/01		X° ±1°
					REV.: D		