


SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
		
OFF	NONE	ON
OPEN	N/A	2-1, 2-3



CIRCUIT: SPST



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NOS. FOR REF. ONLY
- ▲ 4. RATINGS: ANSI/UL 1054 AND CAN/CSA C22.2 NO.55 (E194579):
16A 125VAC [UR, cUR]
10A 250VAC [UR, cUR]
1/3 HP 125/250VAC [UR, cUR]
EN 61058-1:2002:
10(4)A 250V~ μ 1E4 T125/55 [ENEC14]
10(2)A 250V~ μ 5E4 T85/55 [ENEC14]
- ▲ 5. CONTACT MATERIAL: SILVER ALLOY CLAD COPPER
6. CONTACT RESISTANCE: 35m Ω MAX. @ 50VAC INITIAL
7. INSULATION RESISTANCE: 100M Ω MIN. @ 500VDC
8. DIELECTRIC STRENGTH: 1,500 VAC FOR 1 MINUTE
9. ELECTRICAL LIFE: 6,000 CYCLES [UR, cUR]
10,000 CYCLES [ENEC14: 10(4)A 250V~]
50,000 CYCLES [ENEC14: 10(2)A 250V~]
10. TEMPERATURE: -20°C TO 105°C [UR, cUR]
-20°C TO 125°C [ENEC14: 10(4)A 250V~]
-20°C TO 85°C [ENEC14: 10(2)A 250V~]
- ▲ 11. LAMP VOLTAGE: 250V
12. ▲ DENOTES CRITICAL PARAMETER
13. 2011/65/EU (ROHS) COMPLIANT



PANEL THICKNESS	(X) DIMENSION
0.75 TO 1.25	23.3
1.25 TO 2.00	23.6
2.00 TO 3.00	23.9

SUGGESTED PANEL CUTOUT

▲ BODY
COLOR: GREY▲ I / O MARKING
COLOR: WHITE▲ ACTUATOR
LENS COLOR: GREEN

B	23441	REMOVED SEMKO RATING	7/12/18	MJR
A	23265	RELEASE FOR PRODUCTION	3/22/18	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE RE111C4021-137

SCALE

2:1

DATE

3/20/2018

DR

BGL

DWG

38-RE111C4021137

REV

B