



NOTES
Bemerkungen

1

SUITABLE FOR PIN CONTACT SEE DRAWING: TE: 929453
Passend zu Stiftkontakt siehe Zeichnung: TE: 929453

2

FOR FLR-CONDUCTOR ACCORDING TO DIN ISO6722-2 ONLY
Nur fuer FLR-Leitung nach DIN ISO 6722-2

3

DETAILS OF DESIGN ARE LEFT TO MANUFACTURER
Einzelheiten der Ausfuehrung bleiben dem Hersteller ueberlassen

4

TE REVISION AND DIE IDENTIFICATION (E.G. REV. A DIE-NO. 1)
TE Revision und Werkzeug-Nr.(z.B. Rev. A Wkzg.-Nr. 1)

5

Varianten von Design1 werden durch die entsprechenden Versionen von Design2 ersetzt
VARIANTS OF DESIGN1 ARE SUPERSEDED BY CORRESPONDING VERSIONS OF DESIGN2



5-1394702-2	B	1394702-2	A	B6	0.25-0.35	1.2-1.6	Au	A = 2.5 B = 3.6 C = 5.6 D = 13.6 M = 0.2	E = 1.8 G = 1.8 D _{Dr} = 0.8	H = 2.3 K = 2.3 D _{Iso} = 1.4	0.13
5-1394702-1	B	1394702-1	A				Sn				

ORDER NO. DESIGN Bestell-Nr. Ausfuehrung 2	REV	ORDER NO. DESIGN Bestell-Nr. Ausfuehrung 5 1	REV	WIRE SIZE RANGE DGB mm ²	INSULATION Ø Isolations Ø	SURFACE CONTACT AREA Oberflaeche Kontaktzone	LENGTH Laenge mm	WIRE CRIMP Drahtcrimp mm	INSU. CRIMP Iso' Crimp mm	WEIGHT Gewicht g
DIMENSIONS/ Abmessungen										

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0-PLC ± ±0.1

1-PLC ± ±0.1

2-PLC ± ±0.1

3-PLC ± ±0.1

4-PLC ANGLES ±°

MATERIAL FINISH

DWN

R.Schaefer

29JAN2002

CHK

H.Kampmann

29APR2008

APVD

M.Bleicher

29APR2008

PRODUCT SPEC

108-18874

APPLICATION SPEC

114-18021

WEIGHT

-

CUSTOMER DRAWING

NAME

MQS, 2POINT
PRODUCT GROUP DRAWING SOCKET CONTACT
Produktgruppenzeichnung Buchsenkontakt

SIZE

A2

CAGE CODE

00779

DRAWING NO

1534616

RESTRICTED TO

-

SCALE

10:1

SHEET

1

OF

1

REV

B6