





LOC		DIST		REVISIONS			
GP	00	F	LYR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-




SECTION R-R




DETAIL H
SCALE 20:1




SECTION S-S




DETAIL G
SCALE 20:1



DETAIL Z
SCALE 12:1



THIS DRAWING IS UNPUBLISHED. IT IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS TO BE USED ONLY FOR THE PURPOSES SPECIFIED. IT IS NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM. WITHOUT PERMISSION IN WRITING FROM TYCO ELECTRONICS CORPORATION, NO PART OF THIS DRAWING MAY BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM.				DWN R. GRZYBOWSKI 30JAN2009		Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS:				CHK P. D'AMATO 30JAN2009		NAME	
mm				APVD M. PERCHERET 30JAN2009		PRODUCT SPEC	
						APPLICATION SPEC	
						SIZE	
						CAGE CODE	
						DRAWING NO	
						RESTRICTED TO	
						A100779C=2085133	
						SCALE	
						5:1	
						SHEET	
						2	
						OF	
						4	
						REV	
						A	



5.9
MIN

-B-

2X 0.76 X 45°

1.80±0.07

FULL R

⊕	0.07S	C	B	A	⊗
---	-------	---	---	---	---

Technical drawing of a mechanical part. The drawing shows a cross-section of a component with a central vertical feature. Dimensions include a height of 5.9 MIN, a width of 1.05 ± 0.07, and a chamfer of 2X 0.76 X 45°. A label 'FULL R' points to the top surface. A table at the bottom right contains the following information:

⊕	0.07	Ⓢ	C	B	A	Ⓢ
---	------	---	---	---	---	---

RECOMMENDED MATING BOARD
SCALE 4:1

VRM COMPONENT AREA

2X 2.09 MIN

2X 11 MIN

6 MIN

2X 3.7 MIN

Technical drawing of a mechanical part, likely a cross-section of a shaft or a similar component. The drawing includes the following features:

- Section Line:** A diagonal hatching pattern is used to indicate the cross-section of the part.
- Dimension 0.5 MAX:** A dimension line with arrows indicates a maximum length of 0.5 units for a specific feature.
- Dimension 1.57:** A dimension line with arrows indicates a length of 1.57 units for a specific feature.
- Feature -B-:** A label in a box pointing to a specific feature on the part.
- Feature -C-:** A label in a box pointing to a specific feature on the part.
- Feature 30° MAX:** A dimension line with arrows indicates a maximum angle of 30 degrees for a specific feature.
- Feature 7:** A dimension line with arrows indicates a maximum length of 7 units for a specific feature.


Technical drawing of a mechanical part with the following dimensions and tolerances:

- Top left radius: $R0.65$
- Top right vertical dimension: $1.00^{+0}_{-0.13}$
- Bottom horizontal dimension: 4.05 ± 0.10
- Bottom right label: $-B-$

DETAIL N
2X TYPICAL
SCALE 10:1

AMP 4805 REV 31MAR2000

LOC		DIST		REVISIONS					
GP		00		REV	LYR	DESCRIPTION	DATE	DWN	APVD
				-	-	SEE SHEET 1	-	-	-



RECOMMENDED SOLDER LAND GUIDELINE
AS VIEWED FROM CONNECTOR SIDE
SCALE 4:1

THIS DRAWING IS UNPUBLISHED. IT IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS TO BE USED ONLY FOR THE PURPOSES SPECIFIED IN THE DRAWING. IT IS NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM. WITHOUT PERMISSION IN WRITING FROM TYCO ELECTRONICS CORPORATION.		DWN R. GRZYBOWSKI 30JAN2009		Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 9 PLC ±.5 3 PLC ±.5 5 PLC ±.25 4 PLC ±.5 ANGLES ±.2 FINISH		NAME P. D'AMATO 30JAN2009 PRODUCT SPEC APPLICATION SPEC WEIGHT CUSTOMER DRAWING	
MATERIAL		SIZE A100779		DRAWING NO C=2085133	
		SCALE 5:1		SHEET 4 OF 4	
		REV A			