



CIRCUIT: SPST
CONTACT CONFIGURATION

RECOMMENDED P.C.B. LAYOUT

SWITCH FUNCTION		
PDS. 1	PDS. 2	PDS. 3
OFF	NONE	DN
OPEN	NA	3-1

- NOTES:
1. ALL DIMENSIONS IN MM
 2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
 3. TERM. NOS. FOR REF. ONLY
 4. CONTACT RATING: 0.4VA @20VAC or 28VAC or DC
 5. FIXED TERMINAL & MOVING CONTACT:
Cu alloy w/GOLD plate over Nickel.
at full load.
 6. ELECTRIC LIFE: 30,000 make-and-break cycles
 7. INSULATION RESISTANCE: 1,000 M ohm min.
 8. DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
 9. OPERATING TEMP.: -30°C to +85°C
 10. PACKAGE: TRAY/63 PIECES PER TRAY
 11. 2002/95/EC (ROHS) COMPLIANT



B	17337	FIXED PART IN QAD, ADD NOTES	5/30/07	TN	TITLE			
A	12726	RELEASED	1/14/03	CJB	400MSP6R6BLKM7RE			
REV.	ECN No.	DESCRIPTION	DATE	CHKD	SCALE	DATE	DR	DWG
					2:1	5/30/07	TN	T416067
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED								REV
								B