






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		A	INITIAL RELEASED	2016.2.25	A.Y	S.Z



- NOTES:
- PRODUCT SPECIFICATION:
CURRENT RATING: 2.0AMP
CONTACT RESISTANCE: 20mΩ MAX
WITHSTAND VOLTAGE: 1000V AC/DC
INSULATION RESISTANCE: 10E6MΩ MIN
OPERATING TEMPERATURE: -55℃ to +105℃
RECOMMEND SOLDERING PROCESS: WAVE SOLDERING
PEAK TEMPERATURE:250℃
 - MATERIAL
CONTACT: COPPER ALLOY
HOUSING: LOW-TEMPERATURE MATERIAL UL94V-0
 - 1.27um MIN NICKEL PER TEC-112-25 UNDERPLATE ALL OVER
 - 2.54um MIN TIN PER TEC-112-65 ON SOLDERING AREA
 - 0.76um MIN GOLD PER TEC-112-162 ON CONTACT AREA
 - 0.25um MIN GOLD PER TEC-112-162 ON CONTACT AREA
 - 0.076um MIN GOLD FLASH PER TEC-112-33 ON CONTACT AREA
 - PARTS MUST CONFORM TO DIN 41612/IEC60603-2
 - PART NO X-2271084-1,-2 IS NOT RELEASED.



4.57				abc	48	8-2271084-2
4.57				abc	48	8-2271084-1
4.57				abc	48	8-2271084-0
4.57				a c	32	7-2271084-2
4.57				a c	32	7-2271084-1
4.57				a c	32	7-2271084-0
4.0				abc	48	6-2271084-2
4.0				abc	48	6-2271084-1
4.0				abc	48	6-2271084-0
4.0				a c	32	5-2271084-2
4.0				a c	32	5-2271084-1
4.0				a c	32	5-2271084-0
3.0				abc	48	4-2271084-2
3.0				abc	48	4-2271084-1
3.0				abc	48	4-2271084-0
3.0				a c	32	3-2271084-2
3.0				a c	32	3-2271084-1
3.0				a c	32	3-2271084-0
2.5				abc	48	2-2271084-2
2.5				abc	48	2-2271084-1
2.5				abc	48	2-2271084-0
2.5				a c	32	1-2271084-2
2.5				a c	32	1-2271084-1
2.5				a c	32	1-2271084-0
DIM.A	FINISH	ROWS LOADED	POS	PN		



RECOMMENDED P.C.B LAYOUT
(COMPONENT SIDE)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
BO GAO

CHK
KOBBOY ZHAO

APVD
XIANG XU

26SEP2014

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.25
3 PLC ± -
4 PLC ± -
ANGLES ± 3

MATERIAL
SEE NOTE

FINISH
-

PRODUCT SPEC
108-137009

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

NAME
DIN CONNECTOR, TYPE 2C
RECEPTACLE, VERTICAL, WITH CLIPS

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2271084

RESTRICTED TO
-

SCALE
1:1

SHEET
1 of 1

REV
A