


D



C

B

A





NOTCH DESIGNATES
ROW A



1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.

2 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.

3 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER	11 JAN 2011	TE Connectivity	
DIMENSIONS:		CHK J. EABY	11 JAN 2011		
mm		APVD J. EABY	11 JAN 2011	NAME	
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	
		9 PLC ±		APPLICATION SPEC	
		1 PLC ±0.25		SIZE	
		2 PLC ±0.13		CAGE CODE	
MATERIAL		3 PLC ±		DRAWING NO	
		4 PLC ±		RESTRICTED TO	
		ANGLES ±		A100779C=2057764	
		FINISH SEE TABLE		SCALE	
		WEIGHT		6:1	
		CUSTOMER DRAWING		SHEET	
				1 OF 2	
				REV	
				C	

LOC	DIST	REVISIONS					
AD	00	P	LYR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1	-	-	-

	5.5	2057764-6
	4.9	2057764-5
	4.5	2057764-4
	5.5	2057764-3
	4.9	2057764-2
	4.5	2057764-1
FINISH	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER 11 JAN 2011	TE Connectivity	
DIMENSIONS:		CHK J. EABY 11 JAN 2011		
mm		APVD J. EABY 11 JAN 2011	NAME	
		PRODUCT SPEC	IMPACT, 3 PAIR, 8 COLUMN, HEADER UNGUIDED, OPEN END WALL SIGNAL MODULE, 0.39 PTH	
		APPLICATION SPEC		
		WEIGHT		
		CUSTOMER DRAWING		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		SIZE	CAGE CODE	DRAWING NO
9 PLC ±		A1	00779	C=2057764
1 PLC ±0.25		SCALE	5:1	SHEET 2 OF 2
2 PLC ±0.13		REV	C	
3 PLC ±				
4 PLC ±				
ANGLES ±				
FINISH				
SEE TABLE				
MATERIAL				
-				