




TOL. $\pm .010$

COIL: @ 25°C

RESISTANCE 125 OHMS $\pm 10\%$

NOMINAL VOLTAGE 5.0 VDC

MUST OPERATE 2.8 VDC

MUST RELEASE 1.4 VDC MAX, 0.23 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4 MS MAX

RELEASE TIME 2.5 MS MAX

CONTACT STABILIZATION 2.0 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 2/25/98 *EX JERRY* 2/25/98

**COMMUNICATIONS
INSTRUMENTS, INC.**

CUST. OPL
CUST. NO. M39016/10-017P

TYPE "J1MS" RELAY

J1MSW-5XP