







printed on 3 Feb 2021 16:39 (China Standard Time) from TE304429

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
-	-		CI	REVISED	14JUL2010	HMR TM
			D	REVISED	17DEC2012	H.M N.Y
			DI	REVISED	03FEB2021	F.Z R.B



40POS(X-KEY):1-1871315-0



1. MATERIAL: HOUSING: GLASS FIBER THERMO PLASTIC
POLYESTER(94V-0)
COLOR: BLACK
CONTACT: PRE-TIN COPPER ALLOY
RETENTION LEG: PRE-TIN COPPER ALLOY
2. THE SHAPE, SIZE AND POSITION OF THE CHARACTER
SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.

40	X	19	38.0	41.0	42.6	PRE-TIN	1-1871315-0
34	Y	16	32.0	35.0	36.6	PRE-TIN	2-1871315-7
34	X	16	32.0	35.0	36.6	PRE-TIN	1-1871315-7
32	X	15	30.0	33.0	34.6	PRE-TIN	1-1871315-6
30	X	14	28.0	31.0	32.6	PRE-TIN	1-1871315-5
28	X	13	26.0	29.0	30.6	PRE-TIN	1-1871315-4
26	X	12	24.0	27.0	28.6	PRE-TIN	1-1871315-3
24	X	11	22.0	25.0	26.6	PRE-TIN	1-1871315-2
22	X	10	20.0	23.0	24.6	PRE-TIN	1-1871315-1
POS	KEY	n	A	B	C	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.KUDO	23AUG2005	TE Connectivity	
		CHK D.MITSUGI	23AUG2005		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3, ±5°		NAME DYNAMIC D1100 SERIES HDR ASSY, V-TYPE, PRE-TIN 22~40POS	
		0-PLC ±		APVD D.MITSUGI	
		1-PLC ±0.1		PRODUCT SPEC 108-78298 108-137366	
		2-PLC ±0.01		APPLICATION SPEC 114-5377	
		3-PLC ±0.001		SIZE A3	
MATERIAL TBD		4-PLC ±0.0001		CAGE CODE 00779	
		ANGLES ±		DRAWING NO C=1871315	
		FINISH -		RESTRICTED TO -	
		WEIGHT -		SCALE 2:1	
CUSTOMER DRAWING		SHEET 1 OF 3		REV DI	

printed on 3 Feb 2021 16:39 (China Standard Time) from TE304429

D

B

A

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 2020 TE Connectivity. All Rights Reserved. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR













DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1



22POS(X-KEY)
1-1871315-1

24POS(X-KEY)
1-1871315-2

26POS(X-KEY)
1-1871315-3

28POS(X-KEY)
1-1871315-4

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



MATERIAL

TBD

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±0.5
2 PLC ±0.13
3 PLC ±0.013
4 PLC ±0.0001
ANGLES ±-

FINISH

-

DWN

T. KUDO

03DEC2020

CHK

D. MITSUGI

23AUG2005

APVD

D. MITSUGI

23AUG2005

PRODUCT SPEC

108-78298

108-137366

APPLICATION SPEC

114-5377

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME

DYNAMIC D1100 SERIES
HDR ASSY, V-TYPE, PRE-TIN
22~40POS

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1871315

SCALE

2:1

SHEET

2

OF

3

REV

D1

printed on 3 Feb 2021 16:39 (China Standard Time) from TE304429

A

D

4		3		2		1	
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		20			
© COPYRIGHT 2020		TE Connectivity. All Rights Reserved.		ALL RIGHTS RESERVED.			

LOC	DIST	REVISIONS					
-	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1			

30POS(X-KEY)
1-1871315-5

32POS(X-KEY)
1-1871315-6

34POS(X-KEY)
1-1871315-7

15 X 1
TE D1100

16 X 1
TE D1100

17 X 1
TE D1100

30POS(X-KEY)
1-1871315-5

32POS(X-KEY)
1-1871315-6

34POS(X-KEY)
1-1871315-7

NOTES: 2-1871315-7 IS SYMMETRY WITH 1-1871315-7 FOR KEY WAY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	03DEC2020	
CHK		FISHER.ZHU		
APVD		RICK.BIAN		
RICK.BIAN		03DEC2020		
PRODUCT SPEC		108-78298		
APPLICATION SPEC		108-137366		
114-5377				
WEIGHT		-		
CUSTOMER DRAWING				

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm			
0 PLC		±0.5	
1 PLC		±0.13	
2 PLC		±0.013	
3 PLC		±0.0001	
4 PLC		±	
ANGLES		±	
FINISH		-	

MATERIAL		TBD	
FINISH		-	

TE Connectivity		NAME	
DYNAMIC D1100 SERIES		HDR ASSY, V-TYPE, PRE-TIN	
22~40POS			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=1871315	-
SCALE		SHEET	OF
2:1		3	3
REV		D1	

1470-19 (3/11)