






LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			F	REVISED PER ECO-13-010626	31 JUL2013	KH	RP
			G	REVISED PER ECO-19-009248	28 JUN2019	AP	SY



SECTION W-W



O= SIGNAL
⊗= GROUND
RECOMMENDED PCB BOARD
LAYOUT BACKPLANE,
COMPONENT SIDE SHOWN
SCALE 6:1

- △ MATERIAL:
CONTACT - PHOS BRONZE
HOUSING - LCP, UL 94V-0, COLOR - BLACK
- △ FINISH:
CONTACT AREA FINISH CONFORMS TO THE REQUIREMENTS
OF TE PRODUCT SPECIFICATION 108-2303; BASED ON
TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY
LEVEL III, APPLICATIONS IN CONTROLLED
ENVIRONMENTS (CENTRAL OFFICE).
COMPLIANT PIN AREA- 0.5μm MIN MATTE TIN OVER 1.27μm MIN NICKEL.
- △ CONNECTOR MARKED WITH PART NUMBER, DATE CODE
AND STANDARD IN APPROXIMATE AREA SHOWN
- △ DATUMS AND BASIC DIMENSIONS ESTABLISHED BY
CUSTOMER.
- 5. CONTACT AREA LUBRICATED WITH BELLCORE
APPROVED LUBRICANT. TECHNICAL REFERENCE
GR-1217-CORE, ISSUE 1, NOVEMBER 1995.
- △ REFERENCE APPLICATION SPEC 114-13202 FOR RECOMMENDED
PLATED THRU HOLE DIAMETER AND PLATING THICKNESSES.
- △ SHOWN LOGO OR OTHER TE OWNED LOGOS IN APPROXIAMATE AREA.

1934306-1
PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MCMASTER 13JUN2007	TE Connectivity	
DIMENSIONS:		CHK W. DAVIS 13JUN2007		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD W. DAVIS 13JUN2007	NAME	HEADER ASSEMBLY, DOUBLE WALL, 4 PAIR 8 COLUMN TinMan
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	PRODUCT SPEC	SIZE	CAGE CODE DRAWING NO
MATERIAL	FINISH	APPLICATION SPEC	RESTRICTED TO	
		WEIGHT	A100779C=1934306	
CUSTOMER DRAWING		SCALE 10:1	SHEET 1 OF 1	REV G