



5 MATERIAL: HOUSING: PA46 30% GF (BLACK); BOLT: STEEL, TRIVALENT ZINC PLATED (ROHS COMPLIANT); CLIP: STEEL; GROMMET: VMQ

4. THIS PLUG MATES WITH 09D41107L01 THRU 10-\*\*\*\* AND DRC20-50P01 THRU 10 -\*\*\*\* RECEPTACLE. (\*\*\*\* = ALL MODIFICATIONS)

3. FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS SEE ENVELOPE DRAWING 0425-015-0000.

2. RECOMMENDED RETAINING BOLT TORQUE: 25-28 IN-LB [2.82-3.16NM]

1. PLUG IS SUPPLIED WITH DUST CAP. (NOT SHOWN)

NOTES:

REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN
B		REVISED PER PCN-21-118564	07MAR2022	DRK
				IG

DRC26-50S01	DRC26-50S02	DRC26-50S03
01	02	03
DRC26-50S04	DRC26-50S05	DRC26-50S06
04	05	06
DRC26-50S07	DRC26-50S08	DRC26-50S09
07	08	09
DRC26-50S10		
10		

#### KEY ORIENTATION

TCPN	ALIAS PART NUMBER
DRC26-50S01	DRC26-50S01
DRC26-50S02	DRC26-50S02
DRC26-50S03	DRC26-50S03
DRC26-50S04	DRC26-50S04
DRC26-50S05	DRC26-50S05
DRC26-50S06	DRC26-50S06
DRC26-50S07	DRC26-50S07
DRC26-50S08	DRC26-50S08
DRC26-50S09	DRC26-50S09
DRC26-50S10	DRC26-50S10

THIS DRAWING IS A CONTROLLED DOCUMENT.	DWN V. TOMSA 11OCT1994	11OCT1994
DIMENSIONS: INCHES [mm]	CHK D. MEYER 20JUL2000	20JUL2000
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.025 [.64] 4 PLC ± ANGLES ±	APVD R. REED 20JUL2000	R. REED 20JUL2000
108-151052	PRODUCT SPEC	108-151052
APPLICATION SPEC		APPLICATION SPEC
MATERIAL 5	FINISH	FINISH
WEIGHT	-	WEIGHT
CUSTOMER DRAWING		CUSTOMER DRAWING
A2 00779	C=DRC26-50SXX	A2 00779 C=DRC26-50SXX
RESTRICTED TO		RESTRICTED TO
SCALE 3:2	SCALE 3:2	SCALE 3:2
3 OF 1	3 OF 1	3 OF 1
REV B	REV B	REV B