



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G4	REVISED PER ECN-22-156403	03JUN2022	RK	CSD



- 1 MUST BE CRIMPED WITH A 22-18 OR 22-16 P.I.D.G. (RED) TOOL.
- 2 WIRE INSULATION DIA: 0.81-2.08 [.032-.082].
- 3 TONGUE MATERIAL THK: 0.69±0.05 [.027±.002].
- 4 BODY & SLEEVE: TIN/LEAD (93-7) PLATE PER ASTM B545. (3% MIN LEAD CONTENT).
- 5 MATERIAL: BODY & SLEEVE- CU PER ASTM B152 INSULATION - PVF2, COLOR - NATURAL.
- 6 DIMENSION APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.

M7928/4-147, CLASS 1 M7928/13-147, CLASS 1	1000	LOOSE PIECE	53404-1
MILITARY	QTY	PACKAGE TYPE	PART NO.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 150°C[302°F] MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 0.10-0.26mm²[202-509] STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 27MAY05		 TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK T MICHELUTTI 23MAY05				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T MICHELUTTI 23MAY05		NAME TERMINAL, RING TONGUE, PVF2 , PIDG WIRE SIZE: 26-24 AWG	
	0 PLC ± -		PRODUCT SPEC			
	1 PLC ± -		—			
	2 PLC ± 0.20[.008]		APPLICATION SPEC			
	3 PLC ± -		NOT AVAILABLE		SIZE A3	
	4 PLC ± -		WEIGHT —			CAGE CODE 00779
	ANGLES ± -					
MATERIAL		FINISH		RESTRICTED TO —		
					CUSTOMER DRAWING	
						SCALE 4:1
				SHEET 1 of 1		
					REV G4	