










LOC		DIST		REVISIONS				
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD	
		A		RELEASED PER ECO-00-011209	07AUG2017	JM	DT	






- 1 HOUSING:THERMOPLASTIC, UL 94V-0, BLACK.
CONTACTS: COPPER ALLOY, 0.150±0.007 THICK.
- 2 CONFORMS TO REQUIREMENTS OF TE PRODUCT SPECIFICATION 108-32023 BASED ON TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY LEVEL III APPLICATIONS IN CONTROLLED ENVIRONMENTS (CENTRAL OFFICE).
- 3 PLATED THRU HOLE REQUIREMENTS:
FINISHED HOLE = Ø0.360±0.040
DRILLED HOLE = Ø0.450±0.025
COPPER THICKNESS = 0.025 MIN.
IMMERSION TIN IF APPLICABLE = 0.0006-0.0011
- 4 PLATED THRU HOLE DIMENSIONS APPLY TO THE TOP 1.25 OF THE PCB THICKNESS FROM THE CONNECTOR MOUNTING SIDE.
- 5 DATUMS AND BASICS DIMENSIONS ESTABLISHED BY CUSTOMER.
- 6 CONNECTOR MARKED WITH PART NUMBER, DATE CODE, AND "85 OHM" IN APPROXIMATE AREA SHOWN.

TIN	2292385-1
PRESS-FIT TAIL PLATING	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN	J. McCLINTON	16APR2015	 TE Connectivity				
DIMENSIONS:			CHK	D. TROUT	16APR2015					
mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:			NAME	HEADER ASSY, 8 PAIR 12 COLUMN, OPEN END WALL, 85 OHM PiC, STRADA WHISPER				
		0 PLC	±		PRODUCT SPEC					
		1 PLC	±		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO				
		2 PLC	±0.10							
		3 PLC	±		WEIGHT	A100779C=2292385				
		4 PLC	±							
MATERIAL		ANGLES	±		RESTRICTED TO					
		FINISH	SEE TABLE					Customer Drawing		
					SCALE	5:1	SHEET	1 OF 2	REV	A

LOC		DIST		REVISIONS				
GP		00		P	LTR	DESCRIPTION		DATE
						SEE SHEET 1		



THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN	J. McCLINTON	16APR2015	 TE Connectivity			
		CHK	D. TROUT	16APR2015				
DIMENSIONS:		APVD	D. TROUT	16APR2015	NAME			
mm								
					PRODUCT SPEC			
MATERIAL					SIZE			
					CAGE CODE			
					DRAWING NO			
					RESTRICTED TO			
					Customer Drawing			
					SCALE			
					SHEET			
					REV			