

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2000



© COPYRIGHT 2000

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
ISDIST
-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	extra PN added	01AUG2001	BL	KM
	A2	extra PN added + dim c corrected + pack. info	27JUN2003	FH	RL
	A3	extra PN added	05MAR2004	FH	RL
	B	ECR-07-019253	13AUG07	AN	DB
	B1	REVISED PER ECO-10-000445	27JAN10	KK	HMR



6 Maximum, as delivered.

5) Mating face according to DIN 47295/CECC 22240.


4 Minimum dimension.

3) All dimensions are maximum unless otherwise specified.


2 Maximum dimension when fully assembled.

1 Supplied as loose part.

3D VIEW
(assembled status)
3:1



1:1



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±
FINISH	see table
MATERIAL	see table

DWN	02MAR2001
CHK	B. Ienvain
APVD	05APR2001
PRODUCT SPEC	K. Mattheeuws
APPLICATION SPEC	R. Leeman
WEIGHT	-
CUSTOMER DRAWING	114-71024

Tyco Electronics		Tyco Electronics	
CH - Switzerland - Lugano		CH - Switzerland - Lugano	
NAME			
Right angle bulkhead cable jack 1.6/5.6 (75 ohm)			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-3-1393680-0	-

SCALE 5:1 SHEET 1 OF 2 REV B1

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		2000		LOC IS	DIST -	REVISIONS					
© COPYRIGHT 2000		BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.						P	LTR	DESCRIPTION		DATE	DWN
								-	SEE SHEET 1		-	-	-

CROSS REFERENCE TABLE

Old part number	TE part number	Description	Material	Plating	Øa	Øb	dim c	Cable type
V23612-A802-G41	3-1393680-0 7	Outer conductor	Brass	1µm Au min in contact area/min 0.1µm Au over min 2µm NiP	1.7	3.6	15	RG 179 B/U
		Center conductor	CuBe/Bronze	min 0.1µm Au over min 2µm NiP				
		Dielectric	PEEK/PC	-				
V23612-A802-G62	3-1393680-5 7	Outer conductor	Brass	1µm Au min in contact area/min 0.1µm Au over min 2µm NiP	2.15	5.2	15	02XCS(mS) C6Y 0.45/2.0
		Center conductor	CuBe/Bronze	min 0.1µm Au over min 2µm NiP				
		Dielectric	PEEK/PC	-				
V23612-A802-G45	3-1393680-2 7	Outer conductor	Brass	1µm Au min in contact area/min 0.1µm Au over min 2µm NiP	2.55	6.2	15	02YCCY 0.4/2.5 LYC (mS) CY 0.4/2.5
		Center conductor	CuBe/Bronze	min 0.1µm Au over min 2µm NiP				
		Dielectric	PEEK/PC	-				
V23612-A802-G76	3-1393680-7 7	Outer conductor	Brass	1µm Au min in contact area/min 0.1µm Au over min 2µm NiP	2.15	5.2	15	02YS(St) CY 0.45/2.0
		Center conductor	CuBe/Bronze	min 0.1µm Au over min 2µm NiP				
		Dielectric	PEEK/PC	-				
V23612-A802-G76A	3-1393680-8 8	Outer conductor	Brass	1µm Au min in contact area/min 0.1µm Au over min 2µm NiP	2.15	5.2	15	02YS(St) CY 0.45/2.0
		Center conductor	CuBe/Bronze	min 0.1µm Au over min 2µm NiP				
		Dielectric	PEEK/PC	-				
-	1460042-1 9	Outer conductor	Brass	1µm Au min in contact area/min 0.1µm Au over min 2µm NiP	2.15	5.2	15	02YS(St)CY 0.45/2.0
		Center conductor	CuBe/Bronze	min 0.1µm Au over min 2µm NiP				
		Dielectric	PEEK/PC	-				
V23612-A802-G73	4-1393682-3 7	Outer conductor	Brass	1µm Au min in contact area/min 0.1µm Au over min 2µm NiP	1.7	4.3	15	02XSC(St) 6Y 0.37/1.6
		Center conductor	CuBe/Bronze	min 0.1µm Au over min 2µm NiP				
		Dielectric	PEEK/PC	-				
-	1460128-1 8	Outer conductor	Brass	1µm Au min in contact area/min 0.1µm Au over min 2µm NiP	1.35	3.8	15	02YS(St) CHH 0.25/1.2 0.25/1.3 HF 75 0.25/1.15
		Center conductor	CuBe/Bronze	min 0.1µm Au over min 2µm NiP				
		Dielectric	PEEK/PC	-				
-	1460169-1 7 10	Outer conductor	Brass	1µm Au min in contact area/min 0.1µm Au over min 2µm NiP	1.35	3.8	15	02YS(St) CHH 0.25/1.2 0.25/1.3 HF 75 0.25/1.15
		Center conductor	CuBe/Bronze	min 0.1µm Au over min 2µm NiP				
		Dielectric	PEEK/PC	-				

- 7 Individual packaging
8 Tray packaging
9 Bulk packaging
10 Supplied with shrink sleeve 7-1196879-5, 25mm long.
11 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN B. Ienvain 02MAR2001	Tyco Electronics CH - Switzerland - Lugano	
		CHK K. Mattheeuws 05APR2001		
		APVD R. Leeman 05APR2001	NAME Right angle bulkhead cable jack 1.6/5.6 (75 ohm)	
		PRODUCT SPEC -		
		APPLICATION SPEC 114-71024	SIZE A3	
		WEIGHT -		
		CUSTOMER DRAWING	SCALE 5:1	SHEET 2 OF 2
			DRAWING NO 3-1393680-0	RESTRICTED TO -
				REV B1