









P.C. LAYOUT



CIRCUIT: SPST ▲



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERM. NUMBERS FOR REF. ONLY.
4. RATING: 50mA @ 12VDC
- ▲ 5. OPERATING FORCE: $160 \pm 50\text{gf}$
6. TRAVEL: $0.25 + 0.2/-0.1\text{mm}$
7. CONTACT RESISTANCE: $100\text{ m}\Omega$ MAX.
- ▲ 8. CONTACT MATERIAL: SILVER
9. DIELECTRIC STRENGTH: 250V RMS min.
10. INSULATION RESISTANCE: $100\text{ MEGA}\Omega$ min.
11. ELECTRICAL LIFE: 100,000 CYCLES
12. ▲ DENOTES CRITICAL PARAMETER.
13. OPERATING TEMP: -40°C to 85°C
14. PACKAGE: POLYBAG / 750 PIECES PER BAG

C	24508	CHANGE OPERATING TEMPERATURE	9/29/20	JM
B	23227	Added Actuator Diameter	2/19/18	MW
A	20807	RELEASED FOR PRODUCTION	10/03/12	RC
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



E SWITCH®

TITLE	TLE1105F160Q
-------	--------------

SCALE
4:1

DATE	10/3/2012
------	-----------

DR	RC
----	----

DWG
P010100

REV
C