

SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

- Material:
- Item 1 Terminal housing:Thermoplastic (UL 94V-0)
 - Item 2 Clamp: Brass ,Ni plated
 - Item 3 Wire guard solder pin : Brass ,Tin plated
 - Item 4 Terminal screw: Steel, Zinc plating"- "slot type

- Electrical cULus
- Voltage rating: 300VAC
 - Current rating: 10A
 - Wire range:
 - Solid wire(AWG): 12-22
 - Stranded wire(AWG): 12-22
 - Torque(Lb-In): 3.5
 - Screw: M2.5
 - Wire strip length: 6-7mm
 - Withstanding Voltage: 1.6KV
 - Operating temperature: -40°C to +115°C
 - Soldering temperature: 250°C±10°C/5 Sec
 - Safety Approval: 

TI xx 4 1 x A xxxx G

No. OF POLES ————

02: 2 POLES

.....

16: 16 POLES

COLOR ————

0: BLACK

5: GREEN (RAL 6018/T)

6: BLUE

8: GREY (RAL 7035/D)

G: Pb<40000ppm

0000: "@ " Logo (Standard)

000A: "ANYTEK" Mark




Any special item by customer request. please contact sales department.

ANYTEK				CUSTOMER COPY					
				ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD					
TITLE		TI 7.62 SERIES 2P-16P							
PART NO.		Tlxx41xAxxxG		DWG NO.		8TI0401			
APPROVED		CHECKED	DESIGNED	DRAWN		CUST NO.		Tolerance	
			Aaron 2009.06.26	Aaron 2009.06.26		 UNIT: mm SCALE: NONE SHEET: 01/01		X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°	
						REV.: B			

N = Number of poles

DIM A	N×7.62
DIM B	(N-1)×7.62

2p-6p	±0.15
7p-12p	±0.25
13p-16p	±0.35



N=Number of contacts

