


RECOMMENDED P.C.B. LAYOUT





CIRCUIT: SPDT

SWITCH FUNCTION		
<i>POS. 1</i>	<i>POS. 2</i>	<i>POS. 3</i>
		
<i>ON</i>	<i>NONE</i>	<i>ON</i>
<i>2-3</i>	<i>OPEN</i>	<i>2-1</i>

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERM. NOS. FOR REF. ONLY
4. RATING: 5A @120VAC or 28VDC
2A @250VAC
5. FIXED TERMINAL/MOVING CONTACT:
Copper Alloy W/Silver plate.
6. ELECTRICAL LIFE: 50,000 make-and-break
cycles at full load.
7. INSULATION RESISTANCE: 1,000M ohm min.
8. DIELECTRIC STRENGTH: 1000V RMS @sea level
9. OPERATING TEMP.: -30°C to $+85^{\circ}\text{C}$



NO EPOXY ON TERMINALS
BELOW SURFACE C

-C-

E-SWITCH®

B	14399	CORRECT DIMS, UPDATE FORMAT	10/13/04	AR
A	12280	RELEASED	7/1/02	CJB
REV.	ECN No.	DESCRIPTION	DATE	CHKD

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED

<i>E-SWITCH®</i>				
TITLE <i>100 SP-1 T1 B3 M2 Q E</i>				
SCALE <i>2:1</i>	DATE <i>--</i>	DR <i>--</i>	DWG <i>T111088</i>	REV <i>B</i>