


4

3


2

1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



FOR P/N 322870-1 & -3 ONLY

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: SEE TABLE		THIS DRAWING IS A CONTROLLED DOCUMENT.		TE Connectivity					
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: N/A	DIMENSIONS: mm[INCHES]	 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127 [.005] 4 PLC ± - ANGLES ± -	DWN DK SCHRUM 5/25/93	NAME TERMINAL, RING TONGUE, SOLISTRAND AND STRATO-THERM, WIRE SIZE: 2 AWG -				
	FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 26.7-42.4mm² [52,600-83,700] SOLID OR STRANDED		CHK RD HEIM 1/27/94		APVD JL MECKLEY 1/27/94			
FOR ORDER ENTRY		1-800-526-5142		MATERIAL COPPER ASTM B-152 ANNEALED	FINISH SEE TABLE	PRODUCT SPEC 		APPLICATION SPEC -	SIZE A3	CAGE CODE 00779	DRAWING NO C-322870
	CUSTOMER DRAWING							WEIGHT	SCALE 2:1		SHEET 2 of 2