



NOTES:



1. ALL DIMENSION IN MM [INCH]
2. GENERAL TOLERANCE: $X.X=\pm 0.4$
 $X.XX=\pm 0.25$
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING SWITCHING: 150mA, 250V AC/DC
350mA, 110V AC/DC
5. CONTACT RATING (NON-SWITCHING) 5A
6. CONTACT MATERIAL: Silver over Copper Alloy
7. OPERATING FORCE: 425 ± 100 CM/STANDARD
8. OPERATING TEMP.: -30° to 85°C
9. CIRCUIT SP.: 12 POSITIONS, 30° INDEX, CONTINUOUS ROTATION
10. DIELECTRIC STRENGTH 1000V RMS min. @ SEA LEVEL
11. DESIGNATE MAJOR DIMENSIONS
12. LOCK NUT AND WASHER NOT SHOWN.



CONTACT CONFIGURATION
Timing: (MBB) Shorting



RECOMMENDED P.C.B. LAYOUT



E-SWITCH®				TITLE			
C	12220	NEW PART DESC. PER CATALOG	6/11/02	CJB	SCALE	DATE	DR
B	11615	REVISED PART DESCRIPTION	8/15/01	CJB	1.5:1	3/13/01	CJB
REV.	ECN No.	DESCRIPTION	DATE	CHKD			DWG
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND ITS NOT TO BE COPIED OR TRANSFERRED				KC-10-A-(9.5mm) 01-S-P-S			
				G510531			
				REV C			