






REVISIONS						
P	LTR	DESCRIPTION		DATE	DWN	APVD
U		REVISED	PER ECO-21-006948	27OCT2021	RK	MZ



RECOMMENDED PANEL CUTOUT

DETAIL A



DETAIL B

- 1 CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
- 2 WILL ACCEPT FOURTEEN (14) MULTIMATE SOCKET CONTACTS.

OBSOLETE	4-40 THREADED INSERTS	-	-	STANDARD	YES	A	206043-8
OBSOLETE	Ø.150	-	-	SMALL PACK	NO	A	206043-6
-		206043-5	-	STANDARD	YES	B	206043-5
Ø.150		206043-4	206043-1	STANDARD	YES	A	206043-4
-		-	-	STANDARD	NO	B	206043-3
Ø.150		-	206043-1	STANDARD	NO	A	206043-1
DIM C		LASER MARKED OR INK STAMPEDPART NUMBER	MOLDED PART NUMBER	PACKAGING	PERIPHERAL SEAL	SEE DETAIL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN W.LENKER 09/10/92	 TE Connectivity						
				CHK R.STONE 08/11/93							
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		RECEPTACLE ASSEMBLY, REVERSE SEX, SERIES 1, 17-14, CPC —					
INCHES				APVD							
				PRODUCT SPEC 108-10024							
		0 PLC ± — 1 PLC ± — 2 PLC ± 0.13 [.005] 3 PLC ± — 4 PLC ± — ANGLES ± —		APPLICATION SPEC		SIZE CAGE CODE DRAWING NO					
MATERIAL HOUSING: NYLON BLACK		FINISH —		WEIGHT —		A1 00779		C206043		RESTRICTED TO —	
CUSTOMER DRAWING						SCALE 2:1		SHEET 1 OF 1		REV U	