


Number of contacts

96, 64, 32



Male connectors

Identification Number of contacts Contact arrangement Part No. Performance levels according to IEC 60 603-2. Explanation chapter 00

3 2 1

Male connector with solder pins 2.5 mm

96		09 73 196 7902	09 73 196 6902	09 73 196 2902
94 + 2 [▲]		09 73 196 7952	09 73 396 6902 ^{b)}	09 73 196 2952
64		09 73 164 7902	09 73 164 6902	09 73 164 2902
			09 73 364 6902 ^{b)}	09 73 364 2902 ^{b)}
32		09 73 132 7902	09 73 132 6902	09 73 132 2902

Male connector with solder pins 4.0 mm

96		09 73 196 7903	09 73 196 6903	09 73 196 2903
94 + 2 [▲]		09 73 196 7953	09 73 396 6903 ^{b)}	09 73 196 2953
64		09 73 164 7903	09 73 164 6903	09 73 164 2903
			09 73 364 6903 ^{b)}	
32		09 73 132 7903	09 73 132 6903	09 73 132 2903


Male connector with wrap posts 13 mm

96		09 73 196 7907	09 73 196 6907	09 73 196 2907
94 + 2 [▲]		09 73 196 7957	09 73 196 6957	09 73 196 2957
64		09 73 164 7907	09 73 164 6907	09 73 164 2907
32		09 73 132 7907	09 73 132 6907	09 73 132 2907

Male connector with press-in pins

Part Nos. and variants
see chapter 04

Dimensions




a	b
2.5	0.7
4	

Solder pins

a	b
13	0.6



Wrap posts

Panel cut out



Board drillings

Mounting side

Contact arrangement
View from termination side

Dimensions in mm

▲ Male connectors with 2 leading contacts [(0.8 mm) pos. a1 and a32]

Other contact arrangements as well with lagging pins on request

b) Connectors with snap-in clips see chapter 00