




All dimensions are in mm; tolerances according to ISO 2768 m-H

Interface

RPC-1.85 according to
RPC-1.85 mechanically compatible with
Mini-SMP according to

IEC 61169-32
RPC-2.40
MIL-STD-348
Mateable with GPPO™ (Gilbert Engineering Co., Inc.)
and SSMP™ (Connectors Devices, Inc.)

Documents

N/A

Material and plating

Connector parts

Center contact
Outer contact RPC-1.85
Outer contact Mini-SMP
Dielectric

Material

CuBe
Stainless steel
CuBe
PEEK

Plating

Gold, min. 1.27 µm, over chemical nickel
Passivated
Gold, min. 0.8 µm, over chemical nickel

Technical Data Sheet

Rosenberger

Adaptor
RPC-1.85 jack – Mini-SMP jack

08K118-K00S3

Electrical data

Impedance	50 Ω
Frequency	DC to 65 GHz
Return loss	≥ 30 dB, DC to 12 GHz ≥ 18 dB, 12 GHz to 50 GHz ≥ 15 dB, 50 GHz to 65 GHz
Insertion loss	$\leq 0.05 \times \sqrt{f(\text{GHz})}$ dB
Insulation resistance	≥ 5 G Ω
Test voltage (at sea level)	500 V rms
Working voltage (at sea level)	150 V rms

Mechanical data

Mating cycles RPC-1.85	≥ 500
Mating cycles Mini-SMP	
if mating part is Smooth bore	≥ 500
if mating part is Full detent	≥ 100
Center contact captivation	≥ 20 N
Coupling test torque RPC-1.85	1.65 Nm
Recommended torque RPC-1.85	0.80 Nm to 1.10 Nm
Engagement force Mini-SMP	
- Smooth bore	11 N typical
- Full detent	19 N typical
Disengagement force Mini-SMP	
- Smooth bore	11 N typical
- Full detent	29 N typical

Environmental data

Temperature range	-40°C to +85°C
Thermal shock	IEC 61169-1, Subclause 9.4.4
Corrosion	IEC 61169-1, Subclause 9.4.6
Vibration	IEC 61169-1, Subclause 9.3.3
Shock	IEC 61169-1, Subclause 9.3.14
Moisture resistance	IEC 61169-1, Subclause 9.4.3
RoHS	compliant

Tooling

N/A

Suitable cables

N/A

Weight

5.5 g/pce

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Herbert Babinger	05.01.05	F. Reiner	20.06.18	b01	18.1026	M.Ruf	20.06.18

Rosenberger Hochfrequenztechnik GmbH & Co. KG
P.O.Box 1260 D-84526 Tittmoning Germany
www.rosenberger.de

Tel. : +49 8684 18-0
Email : info@rosenberger.de

Page

2 / 2