


RECOMMENDED P.C.B. LAYOUT




CIRCUIT: SPDT



SWITCH FUNCTION			
PDS. 1	PDS. 2	PDS. 3	
DN	NONE	DN	
2-3	OPEN	2-1	

NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- TERM. NOS. FOR REF. ONLY
- RATING: 0.4(VA) Max. @20V Max. (AC OR DC)
- FIXED TERM. & MOVING CONTACT;
COPPER ALLOY W/GOLD PLATE OVER NICKLE PLATE.
- ELECTRICAL LIFE: 50,000 MAKE-AND-BREAK
CYCLES AT FULL LOAD.
- INSULATION RESISTANCE: 1,000M OHM MIN.
- DIELECTRIC STRENGTH: 1000V RMS @SEA LEVEL
- OPERATING TEMP.: -30°C to 85°C
- ▲ DENOTES CRITICAL PARAMETER.
- 2002/95/EC (ROHS) COMPLIANT



PDS. 1 PDS. 3



ADD ROHS NOTE				E-SWITCH®			
C	15491	UPDATE ACTUATOR	11/2/05	PH	TITLE 100SP1T7B13M2RE		
B	14164	RELEASED	7/13/05	AR			
A	13278	DESCRIPTION	7/10/03	AR			
REV.	ECN No.	DATE	CHKD	SCALE	DATE	DR	DWG
				2:1	7/10/03	AR	T110019
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				REV C			