









N=NUMBER OF POLES

DIM		TOL		
		1P--6P	7P--12P	13P--16P
Dim P	(N-1)×7.5	±0.15	±0.25	±0.35
Dim L	N×7.5+1.8	±0.15	±0.25	±0.35



SIGN	DATE	DESCRIPTION	APPROVER
△	09/15'11	The color is changed from RAL7035/D to RAL7004/P	Runner
△	09/15'11	The dimension is changed from 2.1 to 2.2	Runner
△	09/15'11	The Material is changed	Runner
△	09/15'11	The tolerance is changed	Runner
△	09/25'13	change the dimension from 18.6&2.6 to 19.2&3.2	Da cheng
△	09/25'13	change the electrical specification	Da cheng

Material:

- Item ① Terminal body: Thermoplastic (UL94V-0)
- Item ② Terminal side body: Thermoplastic (UL94V-0)
- Item ③ Terminal cover: Thermoplastic (UL94V-0)
- Item ④ Contact pin : Copper, Tin Plated.
- Item ⑤ Spring clamp : Stainless steel
- Item ⑥ Contact pin : Copper, Tin Plated.

- Electrical: cULus
- Voltage rating: 300 V
 - Current rating(Sol): 30 A
 - Current rating(Str): 35 A
 - Solid wire(AWG): 10-24
 - Stranded wire(AWG): 8-24
 - Wire strip length: 15-16 mm
 - Withstanding Voltage: 1.6KV
 - Operating temperature: -40°C to +120°C
 - Soldering temperature: 260°C±5°C/5 Sec
 - Safety Approval: cULus
 - Critical dimension: ▽

NK xx A 0 x 1 xxxx G

End Stackable
01: 1 POLES
02: 2 POLES
16: 16 POLES

- Body Color
- 0 Black (RAL9005)
 - 2 Red (RAL3001/D)
 - 3 Orange(RAL2011/P)
 - 4 Yellow(RAL1018/A)
 - 5 Green(RAL6018/T)
 - 6 Blue (RAL5015/A)
 - 8 Grey(RAL7004/P)
 - 9 White(RAL1102)
 - C Multiple colors

RoHS compliant
(lead<4%)
In copper Alloy
0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	NK 7.5mm Series Vertical (Single tail B type)(第1P左端子靠边型)						
PART NO.	NKxxA0x1xxxxG			DWG NO.	8NK0002		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
		Da cheng 2013.09.25	Da cheng 2013.09.25		UNIT: mm	X.	±0.50
					SCALE: NONE	X.X	±0.30
						X.XX	±0.10
				SHEET: 01/01	REV.: C	X°	±1°