

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Device application	Standard mill switch Universal mill switch Heavy duty
Device short name	T
Series name	Severe duty

### Complementary

[Ith] conventional free air thermal current	20 A
[Ui] rated insulation voltage	600 V
Base plate style	Style A
Body material	Cast zinc
Contact code designation	A600 P600
Contacts material	Silver flashed copper
Contact operation	Snap action
Maximum displacement angle	88 °
Positive opening	Without
Switch actuation	CW
Tilting angle	14 °
Torque value	12 lbf.in
Tripping angle	12 °

### Environment

Ambient air temperature for operation	-10...185 °F
Electrical shock protection class	Class 0
IP degree of protection	IP65 IP66 IP67
NEMA degree of protection	NEMA 1/2/4/12/13
Product certifications	CE CSA UL listed
Protective treatment	Corrosion resistant gray paint
Shock resistance	30 gn
Standards	UL 508

### Ordering and shipping details

Category	21497 - 9007 FT,T OILTIGHT AND FOUNDRY
Discount Schedule	DS1
GTIN	00785901334231
Nbr. of units in pkg.	1
Package weight(Lbs)	2.5

Returnability	N
Country of origin	MX

### Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------