




REV.	DATE	DESCRIPTION
A	01/04/04	UPDATE DRAWING FORMAT
B	03/10/06	MODIFY DESCRIPTION TO "50ohm"



RECOMMENDED
CABLE STRIPPING DIM'S

NOTE:

1. CRIMPED FERRULE
HEX CRIMP SIZE .178"
2. CONTACT PIN TO SOLDER

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex							
8						DRAWN	G.R.S.						03/10/06		
7						CHECKED									
6						ISSUED			PART DESCRIPTION						
5	NUT	BRASS	NICKEL	1					BNC R/A CRIMP PLUG – 50ohm (FOR RG–174/U, 188A/U, 316/U CABLE)						
4	FERRULE	COPPER	NICKEL	1					PART NO.						
3	CONTACT PIN	BRASS	GOLD	1					112178						
2	INSULATOR	DELTRIN	NATURAL	1					DWG. NO.						
1	BODY	BRASS	NICKEL	1				112178.DWG							
	DESCRIPTION	MATERIAL	FINISH	QTY			CAD FILE	C:/112/112178.DWG		REV.	B	SIZE	A	SCALE	NA