







D

C

B


A

D


C

B

A



- 1: WIRE INSULATION :12.7[.500]-14.0[.551]
2: ALUMINUM WIRE CMA: 119500 - 150500
ALUMINUM WIRE mm²: 60.55 - 76.26
3 TONGUE RADIUS FEATURE IS NOT A TOOLING CONTROLLED DIMENSION AND MAY NOT BE A TRUE RADIUS



77 grams	8.34±0.13 [.328±.005]	5/16 or M8	BODY: COPPER ASTM B187 ANNEALED TIN PLATE .0038[.000150] MIN THICK PER MIL-T-10727 INSERT&FUNNEL:BRASS ASTM B36 NICKEL PLATE SAE AMS QQ-N-290A, DATED JULY 2000,.00254 [1.000100] MIN THICK	134594-5
WEIGHT	DIM A	B	MATERIAL&FINISH	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 24JUN2004 JJ. DESPRETZ CHK 24JUN2004 G-ROBERT APVD 24JUN2004 Y. PETRONIN	TE Connectivity	
DIMENSIONS: mm[Inches]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.3 1 PLC ±0.3 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ±5 FINISH -	NAME SEALED COPALUM ASSEMBLY 2/0 AL	
MATERIAL -		PRODUCT SPEC -	SIZE A2	RESTRICTED TO
		APPLICATION SPEC -	CAGE CODE -	
		WEIGHT -	DRAWING NO 134594	
		CUSTOMER DRAWING	SCALE 2:1	SHEET 3 OF 4 REV M

