






RECOMMENDED PCB LAYOUT (THICKNESS: 1.6mm)
DIMENSION TOLERANCE: 1 PLC: ± 0.1 2PLC: ± 0.05)





5. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSELETE	10P8C	RED	50 μ "	3-1734580-4
OBSELETE			30 μ "	3-1734580-3
OBSELETE			15 μ "	3-1734580-2
OBSELETE			6 μ "	3-1734580-1
OBSELETE	10P10C	BLACK	50 μ "	1-1734580-4
			30 μ "	1-1734580-3
			15 μ "	1-1734580-2
			6 μ "	1-1734580-1
OBSELETE	10P8C 	BLACK	50 μ "	1734580-8
			30 μ "	1734580-7
			15 μ "	1734580-6
			6 μ "	1734580-5
 OBSELETE	10P8C	BLACK	50 μ "	1734580-4
			30 μ "	1734580-3
			15 μ "	1734580-2
			6 μ "	1734580-1
	RJ 45	HSG. COLOR	MIN. GOLD THICKNESS	PART NUMBER


SCALE	—	SHEET	1 OF 2	REV	B3
-------	---	-------	--------	-----	----

ANGLES	±
FINISH	

LOC	DIST	REVISIONS					
DW	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1.			



15 Kg	13.5 Kg	100	25	2500 PCS
GROSS WEIGHT	NET WEIGHT	PCS/TRAY	TRAYS /CARTON	QUANTITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN O. HU	01JUN2007	 TE Connectivity			
DIMENSIONS: MM		CHK S. HOU	01JUN2007				
		APVD W.J. KE	01JUN2007	NAME MODULAR JACK, RJ45, 8P8C, SHIELDED, SIDE ENTRY, LOW PROFILE			
		PRODUCT SPEC —					
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		APPLICATION SPEC —		SIZE CAGE CODE DRAWING NO RESTRICTED TO			
MATERIAL		FINISH					
		WEIGHT —		CUSTOMER DRAWING SCALE SHEET REV			
		CUSTOMER DRAWING					