






SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
		
ON	NONE	ON
2-3, 5-6	N/A	2-1, 5-4



CIRCUIT: DPDT



RECOMMENDED PANEL MOUNTING



NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: $x.x \pm 0.4$

 $x.xx \pm 0.25$

- TERM. NUMBERS FOR REFERENCE ONLY

▲ 4. RATING: 0.4VA @ 20V AC MAX.

▲ 5. FIXED TERM. & MOVING CONTACT:
COPPER ALLOY W/GOLD PLATE
OVER NICKEL PLATE

6. ELECTRICAL LIFE: 40,000 MAKE-AND
BREAK CYCLES AT FULL LOAD

7. INSULATION RESISTANCE: 1,000M OHM MIN.

8. DIELECTRIC STRENGTH: 1000V RMS
@ SEA LEVEL

9. OPERATING TEMP: -30°C to 85°C

10. ▲ DENOTES CRITICAL PARAMETER

11. 2002/95/EC (ROHS) COMPLIANT

E-SWITCH®

TITLE 100DP1T1B3VS5RE

C	16078	REVISED AND REDRAWN	6/1/2006	CT
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE	DATE	DR	DWG	REV
2:1	11/19/2002	CB	T121136	C