




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
5	A	REVISED PER ECR-17-006855	23MAY2017	BW	MD


- 1
- MATING TAB THK TO BE 0.51±0.025
[.020±.001].
- 2
- TIN PLATE 0.001016 [.000040] MIN THK.
- 3
- WIRE SIZE IS [#22-#18] AWG.
- 4
- INSULATION RANGE IS 2.29-3.30[.090-.130]
CRIMP WIDTH 3.94[.155] F TYPE



SECTION X-X



SECTION Y-Y



6/6 VO NYLON, NATURAL	1969831-2
4/6 V2 NYLON (150° C) BLACK	1969831-1
MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN R.SMITH 19SEP2016		 TE Connectivity		
DIMENSIONS: mm [INCHES]			CHK M.DIDONATO 19SEP2016				
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME ASSEMBLY, RECEPT, POSI-LOCK, ULTRA-POD, 4.75 [.187] SERIES —			
		APVD M.DIDONATO 19SEP2016					
		PRODUCT SPEC —					
		APPLICATION SPEC —					
		—					
MATERIAL		FINISH	WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
TERMINAL — BRASS HOUSING — SEE TABLE		TERMINAL — TIN HOUSING — SEE TABLE	0.000000	A2	00779	C-1969831	—
CUSTOMER DRAWING					SCALE	SHEET	REV
					5:1	1 of 1	A