


REV. 0
DCO 143342

COIL: @ 25°C	
RESISTANCE	39 OHMS ± 10%
NOMINAL VOLTAGE	5.0 VDC
MUST OPERATE	3.2 VDC
MUST RELEASE	2.3 VDC MAX, 0.6 VDC MIN

ENVIRONMENT:	
VIBRATION	10 CPS TO 3000 CPS @ 30 g's
SHOCK	75 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C
NOTES:	OPERATE TIME 2.0 MS MAX.
	RELEASE TIME 4.0 MS MAX.
	CONTACT BOUNCE 1.5 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO IA
28 VDC RESISTIVE 100,000 OPERATIONS

DR. ASB 12/03/01

CK. *[Signature]* 12/3/01

CII Technologies
advanced control electronic solutions

CUST. QPL
CUST. NO. M39016/20-037L REV.

"JMADD" RELAY

JMAPDD-5XL