








LOC	DIST	REVISIONS					
IR	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
			D	HOUSING RIB STRENGTHENED AND RAWMATERIAL CHANGED TO PA4T	06JAN2012	PS	RRP
			E	ECO-16-001320	13JUN2016	AD	SH





△6 TAPE AND REEL PACKAGING ACCORDING TO EIA 481-3 SPECIFICATIONS.



4 POS. / 4 CONT.		300 PCS ON Ø 360 mm OD REEL. TOP ENTRY ORIENTATION PER DETAIL B		1857884-1	
REMARKS		PACKAGING <span style="border: 1px solid black; padding: 2px;">6</span>		PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN <u>Shrivathsa</u> 14 Jul 08 CHK <u>Premjith</u> 14 Jul 08 APVD <u>M Oppers</u> PRODUCT SPEC 108-19117 APPLICATION SPEC 114-19041		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		NAME INVERTIBLE MODULAR JACK, 4 POSITION HANDSET SURFACE MOUNT APPLICATION	
MATERIAL - SEE NOTE 3		FINISH - SEE NOTE 2		SIZE CAGE CODE DRAWING NO A2 C-1857884	
		WEIGHT 1.92 gr		RESTRICTED TO -	
		CUSTOMER DRAWING		SCALE 3.1 SHEET 1 OF 2 REV F	



—DASHLINE INDICATES OUTLINE  
OF JACK, CONTACTS AND BRACKET

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN <u>Shrivathsa</u> 14 Jul 06 CHK <u>PREmjith</u> 14 Jul 06		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±. 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH -		NAME <b>INVERTIBLE MODULAR JACK, 4 POSITION HANDSET SURFACE MOUNT APPLICATION</b>	
		APVD <u>M Oppers</u> PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		SIZE A2 CAGE CODE DRAWING NO C-1857884 RESTRICTED TO -	
MATERIAL -		CUSTOMER DRAWING		SCALE 5:1 SHEET 2 OF 2 REV F	