









REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




5 RECOMMENDED PCB LAYOUT
TOLERANCE ± 0.05 (TOP VIEW)



SECTION A-A

OBSOLETE	9	1734531-9
POSITION NUMBER	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN O.HU 05JUL2005		TE Connectivity Ltd.							
		CHK S.HOU 05JUL2005									
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.5 1 PLC ± 0.2 2 PLC ± 0.1 3 PLC ± 0.05 4 PLC ± - ANGLES ± 3°		NAME							
				APVD W.J.KE 05JUL2005							
				PRODUCT SPEC 108-57197							
				APPLICATION SPEC —							
				SIZE A3							
MATERIAL SEE SHEET 1		FINISH SEE SHEET 1		CAGE CODE 00779		DRAWING NO C-1734531		RESTRICTED TO —			
		WEIGHT —									
CUSTOMER DRAWING						SCALE 1:1		SHEET 2 OF 3		REV D5	

4

3

2

1

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

-,-







COPYRIGHT - By -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



OBSOLETE	1050	150	7	80	8	-0
	1050	150	7	78	7	-8
	1050	150	7	76	7	-6
	1200	150	8	74	7	-4
	1200	150	8	72	7	-2
	1200	150	8	70	7	-0
	1200	150	8	68	6	-8
	1350	150	9	66	6	-6
	1350	150	9	64	6	-4
	1350	150	9	62	6	-2
	1500	150	10	60	6	-0
	1500	150	10	58	5	-8
	1500	150	10	56	5	-6
	1650	150	11	54	5	-4
OBSOLETE	1650	150	11	52	5	-2
	1800	150	12	50	5	-0
	1800	150	12	48	4	-8
	1950	150	13	46	4	-6
	1950	150	13	44	4	-4
	2100	150	14	42	4	-2
	2100	150	14	40	4	-0
	2250	150	15	38	3	-8
OBSOLETE	2400	150	16	36	3	-6
	2550	150	17	34	3	-4
	2700	150	18	32	3	-2
	2850	150	19	30	3	-0
	3150	150	21	28	2	-8
OBSOLETE	3300	150	22	26	2	-6
	3600	150	24	24	2	-4
	3900	150	26	22	2	-2
	4350	150	29	20	2	-0
	4800	150	32	18	1	-8
	5400	150	36	16	1	-6
	6150	150	41	14	1	-4
	7200	150	48	12	1	-2
	8550	150	57	10	1	-0
OBSOLETE	8550	150	57	9		1734531-9
OBSOLETE	10650	150	72	8		1734531-8
	14400	150	96	6		1734531-6
	21600	150	144	4		1734531-4
	QTY	TUBE/ CARTON	PCS/ TUBE	POSITION NUMBER	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN O.HU 05JUL2005	TE Connectivity Ltd.			
		CHK S.HOU 05JUL2005				
		APVD W.J.KE 05JUL2005	NAME AMPMODU 2.0mm PITCH,RCPT CONN., RIGHT-ANGLE, MOUNT TYPE			
		PRODUCT SPEC 108-57197				
		APPLICATION SPEC -	SIZE A3 CAGE CODE 00779 DRAWING NO C-1734531 RESTRICTED TO -			
		WEIGHT -				
		CUSTOMER DRAWING	SCALE 1:1 SHEET 3 of 3 REV D5			

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± 0.5 1 PLC ± 0.2 2 PLC ± 0.1 3 PLC ± 0.05 4 PLC ± - ANGLES ± 3°
MATERIAL SEE SHEET 1	FINISH SEE SHEET 1